

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

95522-2887

Status:

Active

Overview:

Modular Plugs - Jacks

Description:

Modular Jack, High Profile Top Entry with Ribs, 8/8 Circuits, Gold (Au)

Documents:

3D Model

Drawing (PDF)

Test Summary STR-1425 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E107635

General

Product Family

Series

Component Type

Magnetic

Overview

Performance Category

Power over Ethernet (PoE)

Product Name

UPC

Modular Jacks/Plugs

95522

PCB Jack

No

Modular Plugs - Jacks

3

N/A

RJ45

800756740874

Physical

Color - Resin

Durability (mating cycles max)

Flammability

Inverted / Top Latch

Jack Height

Lightpipes/LEDs

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Net Weight

Orientation

PCB Locator

PCB Retention

PCB Thickness - Recommended

Packaging Type

Pitch - Mating Interface

Pitch - Termination Interface

Ports

Positions / Loaded Contacts

Surface Mount Compatible (SMC)

Temperature Range - Operating

Termination Interface: Style

Waterproof / Dustproof

Wire/Cable Type

Black

500

94V-0

N/A

16.25mm

None

Copper Alloy

Gold

Tin

High Temperature Thermoplastic

3.390/g

Vertical (Top Entry)

Yes

Yes

1.57mm

Tray

1.02mm

1.27mm

1

8/8

Yes

-40°C to +80°C

Through Hole

No

N/A

Electrical

Current - Maximum per Contact

Shielded

Voltage - Maximum

1.5A


No

125V DC

Solder Process Data

Duration at Max. Process Temperature (seconds)

5



EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com

For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

95522Series

Mates With

90075 Modular Plug

Lead-free Process Capability	Wave Capable (TH only)
Max. Cycles at Max. Process Temperature	1
Process Temperature max. C	260

Material Info

Reference - Drawing Numbers

Sales Drawing	SD-95522-001
Test Summary	STR-1425

This document was generated on 04/03/2015

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION