






Global Connector Technology Ltd. - USB2070: Mini USB Receptacle, Type A/B, 10 Pin, SMT, Horizontal



RECOMMENDED P.C.B LAYOUT

GENERAL TOLERANCE: ± 0.05
 AS VIEWED FROM COMPONENT SIDE



SECTION A-A

Specifications 规格:

Materials 物料规格:

- Plastic Housing 塑胶外壳: LCP UL94V-0 Black \triangle
 LCP UL94V-0, 黑色
- Contact Terminal 接触端子: Phosphor Bronze 磷青铜
- Metallic Shell 金属外壳: Brass 黄铜 \triangle

Plating 电镀规格:

- Contact Terminal plating 接触端子部分电镀:
 Underplating 底层电镀: Nickel all over 全部镀镍
 Contact Area 接触部分: 15 μ " Gold 镀金15 μ "
 Solder Tails 焊接末端: Tin 50 μ " 镀锡50 μ " \triangle
- Metallic Shell plating 金属外壳电镀:
 Underplating 底层电镀: 50 μ " Min. Nickel all over 全部镀镍最少50 μ "
 Finish 表面处理: Matte Tin 50 μ " all over 整体镀雾锡50 μ " \triangle

Electrical 电气规格:

- Voltage Rating 电压额定值: 30VDC
- Current Rating 电流额定值: 1A
- Operating Temperature 工作温度: -50°C to +85°C \triangle \triangle
- Contact Resistance 接触电阻值: 50mW Max.
- Insulation Resistance 绝缘电阻值: 100MW Min (Apply施加100VDC)
- Dielectric Withstanding Voltage 耐电压: No Discharge or Flash没有放电或火花 (100VAC is applied for 1 min. 施加100VAC共一分钟)

Mechanical 机械性规格:

- Mating Force 插入力: 35N (3.57KgF) Max.
- Unmating Force 拔出力: 7N (0.71KgF) Min. - 1st mating cycle \triangle
- Unmating Force 拔出力: 3N (0.31KgF) Min. - 5001st mating cycle \triangle
- Durability 耐久性: 5,000 Cycles 5,000次插拔 \triangle

Ordering Grid

USB2070 - 10 - RCHM - 15 - STB - 00 - 00 - A REQUEST SAMPLES AND QUOTATION

No. of Contacts
10

Contact Plating
15 = 15 μ " Gold

Packing Options
A = Tape & Reel (With Mylar)
(Quantity per Reel: 800pcs)

00 = Without Post
Offset
00 = No Offset

Tolerances (Except as noted)	Part Number:- USB2070	Date:- 13 MAR 08
Dimensions in mm X.X \pm 0.35 X.X° \pm 1° X.XX \pm 0.25 X.X° \pm 0.5° X.XXX \pm 0.150 X.XX° \pm 0.25°	Description:- MINI USB RECEPTACLE, TYPE A/B, 10 PIN, SMT, HORIZONTAL	
	THIS DRAWING IS CONFIDENTIAL AND MUST NOT BE COPIED OR DISCLOSED WITHOUT WRITTEN CONSENT	
Third Angle Projection	Scale NTS	Revision E


GCT

www.globalconnectortechology.com

By	LYH	ASE	ASE	SA	ASE
DETAIL	DRAWING RELEASE	ECN080331A	ECN080922A	PCN20101004-2	PCNUSB2070-001
REV	A	B	C	D	E
DATE	13/03/08	31/03/08	22/09/08	04/11/10	07/12/11

Scale NTS	Revision E	Material See Note	Drawn by LYH	Sheet No. E & OE 1/2
--------------	---------------	----------------------	-----------------	----------------------------

Global Connector Technology Ltd. - USB2070: Mini USB Receptacle, Type A/B, 10 Pin, SMT, Horizontal



Notes 注意:

1. All dimensions in millimeters 所有尺寸均是毫米
2. Each cavity will hold 1pc. Placement methods are shown in the diagrams. 每穴放置1pc产品, 放置方式如图所示
3. The peel-off force between the COVER TAPE & CARRY TAPE is: 0.1N-0.7N (variation within 0.3N). Peel-off angle: 160-180 degree. COVER TAPE 与 CARRY TAPE 剥离力: 0.1N-0.7N (跳动量在0.3N以内) 剥离角度: 160-180度; 剥离速度
4. Component Load Per 13" Reel: 800Pcs 每13"卷筒承载零件: 800件

Packing Rules 封装规则:

1. All the labels on REEL should be face-up
Reel 标签一律朝上
2. Place 11 filled REEL into the bag
以11盘作为一个包装单位, 外包PE袋
3. Insert bag into outer box
卷盘使用塑胶袋封装; 然后放入外箱
4. Stick label on the outer carton
标签贴放箱外

By	LYH	ASE	ASE	SA	ASE
DETAIL	DRAWING RELEASE	ECN080331A	ECN080922A	PCN20101004-2	PCNUSB2070-001
REV DATE	A 13/03/08	B 31/03/08	C 22/09/08	D 04/11/10	E 07/12/11



Tolerances (Except as noted)	Part Number:- USB2070	Date:- 13 MAR 08
Dimensions in mm	Description:- MINI USB RECEPTACLE, TYPE A/B, 10 PIN, SMT, HORIZONTAL	
Third Angle Projection	© THIS DRAWING IS CONFIDENTIAL AND MUST NOT BE COPIED OR DISCLOSED WITHOUT WRITTEN CONSENT	

GCT					www.globalconnectortech.com
Scale NTS	Revision E	Material See Note	Drawn by LYH	E & OE	Sheet No. 2/2