### IEC Appliance Inlet C14 or C18 with Filter, ECO design, Front- or Rear Side Mounting

Standard- or Medical-Filter







Screw-on mounting PCB snap-in version

Snap-in mounting Quick connect terminals 6.3 x 0.8 mm Protection class II

Screw-on mounting with wires (stranded)













### **Description**

- Panel Mount:

Screw-on version from front or rear side, snap-in version from front side, PCB Version from rear side

- 2 Functions:

Appliance Inlet protection class I or II, Line filter in standard and medical version

- Solder, quick connect or wire (stranded)
- PCB Mounting
- Earth Terminal

## **Approvals**

- VDE Certificate Number: 40016382

- UL File Number: E72928

- CCC File Number: 2010010204438235

### **Characteristics**

- Compact high performance filter
- Optimal shielding due to completely closed filter case, unpotted
- Designed for standard and medical applications
- Suitable for assembly in metal plated plastic housings
- Suitable for use in equipment according to IEC/UL 60950 Suitable for use in medical equipment according to IEC/UL 60601-1

### Other versions on request

- Snap-in for panel thickness >2mm to 3mm
- flexible wire with various lenghts
- Class X1- and Y1-capacitors for enhanced withstand voltage
- Medical version M80
- Variant with notch for V-Lock mating Cordsets

### References

Alternative: version without line filter 6100-3

### Weblinks

pdf-datasheet, html-datasheet, General Product Information, RoHS, CHINA-RoHS, REACH, Mating Connectors, e-Shop, SCHURTER-Stock-Check, Distributor-Stock-Check, Accessories, Wire Harnessing

Newly available variants corresponding to V-Lock mating cordset. The connector is equipped with a notch intended for use with the latching cordset. The cord latching system prevents against accidental removal of the cordset.


### **Technical Data**

Ratings IEC	1 - 10 A @ Ta 40 °C / 250 VAC; 50 Hz
Ratings UL/CSA	1 - 15 A @ Ta 40 °C / 250 VAC; 60 Hz
Leakage Current	standard < 0.5 mA (250 V / 60 Hz) medical < 5 µA (250 V / 60 Hz)
Dielectric Strength	> 1.7 kVDC between L-N > 2.7 kVDC between L/N-PE Test voltage (2 sec)
Allowable Operation Temp.	-25 °C to 85 °C
Climatic Category	25/085/21 acc. to IEC 60068-1
Degree of Protection	from front side IP 40 acc. to IEC 60529
Protection Class	Suitable for appliances with protection class I or II acc. to IEC 61140
Terminal	Quick connect terminals 6.3 x 0.8 mm Solder terminals Flexible wire AWG18 (15A AWG16), 150 mm
Panel Thickness s	Screw: max 8 mm Mounting screw torque max 0.5 Nm Snap-in: 0.8 mm to 2 mm (all steps with one variant)
Material: Housing	Themoplast / steel tin-plated, black / metallic, UL 94V-0


Appliance-Inlet/-Outlet	C14 / C18 acc. to IEC 60320,
	UL 498, CSA C22.2 no. 42 (for cold
	conditions) pin-temperature 70 °C, 10 A,
	Protection Class I or II
Line Filter	Standard and Medical Version, IEC
	60939, UL 1283, CSA C22.2 no. 8
	Technical Details
MTBF	> 3'000'000 h acc. to MIL-HB-217 F

## **Dimension**

Front or rear side mounting for screws with nuts or blind rivets (panel cutout for frontside mounting)




Rear side mounting with pre-formed, threaded holes for M3 screws (panel cutout for rear side mounting)




Dimensions for class II version also apply to class I

Snap-in mounting from front side




Dimensions for class I version also apply class II


# PCB snap-in rear side mounting, protection class I




# PCB rear side mounting, protection class I




# PCB snap-in rear side mounting, protection class II



PCB rear side mounting, protection class II



# Screw and snap-in mounting with flexible wire



- 1) Flexible wire, standard length 150 mm or special length on request 2) Nonexistent for protection class  ${\sf II}$

- 3) Panel cut-out screw-on version, back-side mounting
  4) Panel cut-out screw-on version, front- or back-side mounting
- 5) Panel cut-out snap-in version, front-side mounting


# **Technical Data of Filter-Components**


<b>R [M</b> Ω]	Capacitance CY [nF]	Capacitance CX [nF]	Inductances L [mH]	Filter-Type	Rated Current [A]
-	2.2	100	2 x 12	Standard Version	1
-	2.2	100	2 x 5.2	Standard Version	2
-	2.2	100	2 x 2	Standard Version	4
-	2.2	100	2 x 0.8	Standard Version	6
-	2.2	100	2 x 0.4	Standard Version	10
-	2.2	100	2 x 0.1	Standard Version	15
1	-	100	2 x 12	Medical Version (M5)	1
1	-	100	2 x 5.2	Medical Version (M5)	2
1	-	100	2 x 2	Medical Version (M5)	4
1	-	100	2 x 0.8	Medical Version (M5)	6
1	-	100	2 x 0.4	Medical Version (M5)	10
1	-	100	2 x 0.1	Medical Version (M5)	15
1	2.2	100	2 x 12	Bleed Resistor Version	1
1	2.2	100	2 x 5.2	Bleed Resistor Version	2
1	2.2	100	2 x 2	Bleed Resistor Version	4
1	2.2	100	2 x 0.8	Bleed Resistor Version	6
1	2.2	100	2 x 0.4	Bleed Resistor Version	10
1	2.2	100	2 x 0.1	Bleed Resistor Version	15

# **Diagrams**

Standard version

Bleed resistor version





1) Line


2) Load


1) Line 2) Load

4 A

Medical version M5

Medical version M5, prot. class II





6 A

1) Line 2) Load 2) Load

2 A


15 A

# **Attenuation Loss** Standard version

- - - - differential mode \_\_\_\_\_ common mode


dB 80 60

4B 80 60 40 20 40 40 20 0 0.01 0.1 1 10 100 400 MHz



10 A

1 A




dB 80 60 40 20 Medical version (M5)


1 A



4 A





6 A



10 A







# All Variants

Rated Cur- rent [A]	Filter-Type	Mounting	Mounting side	Terminal	Protection Class	Order Number
6	Standard Version	Snap-in 2 - 3 mm	Front Side	Flexible wire	I	5120.3034.0
1	Standard Version	Snap-in	Front Side	Quick connect	I	5120.2000.0
2	Standard Version	Snap-in	Front Side	Quick connect	1	5120.2001.0
4	Standard Version	Snap-in	Front Side	Quick connect	I	5120.2003.0
6	Standard Version	Snap-in	Front Side	Quick connect	1	5120.2004.0
10	Standard Version	Snap-in	Front Side	Quick connect	I	5120.2006.0
10	Standard Version	Snap-in	Front Side	Flexible wire and	1	5120.2046.0
15	Standard Version	Snap-in	Front Side	Quick connect	I	5120.2007.0
1	Standard Version	Screw/PCB snap-in	Rear Side	PCB pin and earth	I	5120.5070.0
2	Standard Version	Screw/PCB snap-in	Rear Side	PCB pin and earth	I	5120.5071.0
4	Standard Version	Screw/PCB snap-in	Rear Side	PCB pin and earth	I	5120.5073.0
6	Standard Version	Screw/PCB snap-in	Rear Side	PCB pin and earth	I	5120.5074.0
10	Standard Version	Screw/PCB snap-in	Rear Side	PCB pin and earth	I	5120.5076.0
15	Standard Version	Screw/PCB snap-in	Rear Side	PCB pin and earth	1	5120.5077.0
1	Standard Version	Screw/PCB	Rear Side	PCB pin and earth	I	5120.4070.0
2	Standard Version	Screw/PCB	Rear Side	PCB pin and earth	1	5120.4071.0
4	Standard Version	Screw/PCB	Rear Side	PCB pin and earth	I	5120.4073.0
6	Standard Version	Screw/PCB	Rear Side	PCB pin and earth	1	5120.4074.0
10	Standard Version	Screw/PCB	Rear Side	PCB pin and earth	I	5120.4076.0
15	Standard Version	Screw/PCB	Rear Side	PCB pin and earth	I	5120.4077.0
1	Standard Version	Screw-on/Rivet	Front-/Rear-Side	Quick connect	I	5120.0000.0
1	Standard Version	Screw-on/Rivet	Front-/Rear-Side	Solder terminals	I	5120.0010.0
2	Standard Version	Screw-on/Rivet	Front-/Rear-Side	Quick connect	I	5120.0001.0
4	Standard Version	Screw-on/Rivet	Front-/Rear-Side	Quick connect	I	5120.0003.0
6	Standard Version	Screw-on/Rivet	Front-/Rear-Side	Quick connect	I	5120.0004.0
10	Standard Version	Screw-on/Rivet	Front-/Rear-Side	Quick connect	I	5120.0006.0
15	Standard Version	Screw-on/Rivet	Front-/Rear-Side	Quick connect	I	5120.0007.0
15	Standard Version	Screw-on/Rivet	Front-/Rear-Side	Flexible wire	I	5120.0057.0
1	Standard Version	Screw	Rear Side	Quick connect	I	5120.1000.0
2	Standard Version	Screw	Rear Side	Quick connect	1	5120.1001.0
4	Standard Version	Screw	Rear Side	Quick connect	I	5120.1003.0
6	Standard Version	Screw	Rear Side	Quick connect	1	5120.1004.0
10	Standard Version	Screw	Rear Side	Quick connect	1	5120.1006.0
10	Standard Version	Screw	Rear Side	Quick connect	I	5120.1006.0.21
10	Standard Version	Screw	Rear Side	Flexible wire and	I	5120.1046.0

ated Cur- rent [A]	Filter-Type	Mounting	Mounting side	Terminal	Protection Class	Order Number
15	Standard Version	Screw	Rear Side	Quick connect	I	5120.1007.0
1	Medical Version (M5)	Snap-in	Front Side	Quick connect	I	5120.2300.0
2	Medical Version (M5)	Snap-in	Front Side	Quick connect	1	5120.2301.0
4	Medical Version (M5)	Snap-in	Front Side	Quick connect	I	5120.2303.0
6	Medical Version (M5)	Snap-in	Front Side	Quick connect	I	5120.2304.0
10	Medical Version (M5)	Snap-in	Front Side	Quick connect	1	5120.2306.0
15	Medical Version (M5)	Snap-in	Front Side	Quick connect	I	5120.2307.0
4	Medical Version (M5)	Screw/PCB snap-in	Rear Side	PCB pin and earth	1	5120.5373.0
6	Medical Version (M5)	Screw/PCB snap-in	Rear Side	PCB pin and earth	I	5120.5374.0
4	Medical Version (M5)	Screw/PCB	Rear Side	PCB pin and earth	I	5120.4373.0
6	Medical Version (M5)	Screw/PCB	Rear Side	PCB pin and earth	ı	5120.4374.0
1	Medical Version (M5)	Screw-on/Rivet	Front-/Rear-Side	Quick connect	ı	5120.0300.0
2	Medical Version (M5)	Screw-on/Rivet	Front-/Rear-Side	Quick connect	ı	5120.0301.0
4	Medical Version (M5)	Screw-on/Rivet	Front-/Rear-Side	Quick connect	ı	5120.0303.0
4	Medical Version (M5)	Screw-on/Rivet	Front-/Rear-Side	Flexible wire and	ı	5120.0343.0
6	Medical Version (M5)	Screw-on/Rivet	Front-/Rear-Side	Quick connect	i	5120.0304.0
10	Medical Version (M5)	Screw-on/Rivet	Front-/Rear-Side	Quick connect	·	5120.0306.0
15	Medical Version (M5)	Screw-on/Rivet	Front-/Rear-Side	Quick connect	ı	5120.0307.0
1	Medical Version (M5)	Screw	Rear Side	Quick connect	i I	5120.1300.0
2	Medical Version (M5)	Screw	Rear Side	Quick connect	<u>'</u> I	5120.1300.0
4	, ,		Rear Side	Quick connect	' 	5120.1301.0
	Medical Version (M5)	Screw				
6	Medical Version (M5)	Screw	Rear Side	Quick connect	l	5120.1304.0
10	Medical Version (M5)	Screw	Rear Side	Quick connect	l	5120.1306.0
10	Medical Version (M5)	Screw	Rear Side	Quick connect	. I	5120.1306.0.21
10	Medical Version (M5)	Screw	Rear Side	Flexible wire and	l .	5120.1346.0
15	Medical Version (M5)	Screw	Rear Side	Quick connect	1	5120.1307.0
1	Medical Version (M5)	Snap-in	Front Side	Quick connect	II	5120.2300.1
2	Medical Version (M5)	Snap-in	Front Side	Quick connect	II	5120.2301.1
4	Medical Version (M5)	Snap-in	Front Side	Quick connect	II	5120.2303.1
6	Medical Version (M5)	Snap-in	Front Side	Quick connect	II	5120.2304.1
10	Medical Version (M5)	Snap-in	Front Side	Quick connect	II	5120.2306.1
15	Medical Version (M5)	Snap-in	Front Side	Quick connect	II	5120.2307.1
4	Medical Version (M5)	Screw/PCB snap-in	Rear Side	PCB pin and earth	II	5120.5373.1
6	Medical Version (M5)	Screw/PCB snap-in	Rear Side	PCB pin and earth	II	5120.5374.1
10	Medical Version (M5)	Screw/PCB snap-in	Rear Side	PCB pin and earth	II	5120.5376.1
4	Medical Version (M5)	Screw/PCB	Rear Side	PCB pin and earth	II	5120.4373.1
6	Medical Version (M5)	Screw/PCB	Rear Side	PCB pin and earth	II	5120.4374.1
2	Medical Version (M5)	Screw-on/Rivet	Front-/Rear-Side	Quick connect	II	5120.0301.1
4	Medical Version (M5)	Screw-on/Rivet	Front-/Rear-Side	Quick connect	II	5120.0303.1
6	Medical Version (M5)	Screw-on/Rivet	Front-/Rear-Side	Quick connect	II	5120.0304.1
10	Medical Version (M5)	Screw-on/Rivet	Front-/Rear-Side	Solder terminals	II	5120.0316.1
1	Medical Version (M5)	Screw	Rear Side	Quick connect	II	5120.1300.1
2	Medical Version (M5)	Screw	Rear Side	Quick connect	II	5120.1301.1
2	Medical Version (M5)	Screw	Rear Side	Solder terminals	II	5120.1311.1
4	Medical Version (M5)	Screw	Rear Side	Quick connect	II	5120.1303.1
6	Medical Version (M5)	Screw	Rear Side	Quick connect	II	5120.1304.1
10	Medical Version (M5)	Screw	Rear Side	Quick connect	ll	5120.1306.1
2	Bleed Resistor Version	Snap-in	Front Side	Quick connect	i I	5120.2201.0
4	Bleed Resistor Version	Snap-in	Front Side	Quick connect	i I	5120.2203.0
6	Bleed Resistor Version	Snap-in	Front Side	Quick connect	·	5120.2204.0
10	Bleed Resistor Version	Snap-in	Front Side	Quick connect	i I	5120.2204.0
15	Bleed Resistor Version	Snap-in	Front Side	Quick connect	ı I	5120.2207.0
15	Bleed Resistor Version	Snap-in	Front Side	Quick connect	ı	5120.2207.0
10	Bleed Resistor Version	Screw-on/Rivet	Front-/Rear-Side	Solder terminals	l I	5120.2207.0.21

D : 10	F11 T					0 1 11 1
Rated Cur-	Filter-Type	Mounting	Mounting side	Terminal	Protection Class	Order Number
rent [A]						
ient [A]						

Most Popular.

 $A \textit{vailability} for \textit{all} \textit{products} \textit{can} \textit{be} \textit{searched} \textit{real-time:} \textit{http://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER} \textit{all} \textit{products} \textit{can} \textit{be} \textit{searched} \textit{real-time:} \textit{http://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER} \textit{all} \textit{products} \textit{can} \textit{be} \textit{searched} \textit{real-time:} \textit{http://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER} \textit{all} \textit{products} \textit{can} \textit{be} \textit{searched} \textit{real-time:} \textit{http://www.schurter.com/en/Stock-Check-SCHURTER} \textit{all} \textit{can} \textit{$ 

- 15 A version only according UL/CSA
- Type for screw-on mounting from rear side has pre-threaded holes for M3 screws

Suffix ".21" corresponds to the version with V-Lock mating cordset. The connector is equipped with a notch intended for use with the latching cordset. The cord latching system prevents against accidental removal of the cordset.

Packaging unit

10 Pcs

### **Accessories**

### Description



Assorted Covers Rear Cover



Wire Harness Wire harness for SCHURTER products



# **Mating Outlets/Connectors**

## Category / Description



## Appliance Outlet Overview complete

IEC Appliance Outlet F, Screw-on Mounting, Front Side, Solder Terminal	4787
IEC Appliance Outlet F, Snap-in Mounting, Front Side, Solder or Quick-connect Terminal	4788
IEC Appliance Outlet F or H, Screw-on Mounting, Front Side, Solder, PCB or Quick-connect Terminal	5091

Appliance Outlet further types to 5120

VAC13KS

### Connector Overview complete



IEC Connector C15A, Rewireable, Straight	0102
IEC Connector C15A, Rewireable, Straight	0102-G
IEC Connector C15A, Rewireable, Angled	0112
IEC Connector C13, Rewireable, Angled	4012
IEC Connector C13, Rewireable, Straight	4022
Connector further types to 5120	

# **Mating Outlets/Connectors shuttered**



Power Cord Overview complete

Overview Power Supply Cord with IEC Connector C13, V-Lock, straight

Power Cord further types to 5120

