



### Model Number


**V15-GK-PG9**

Female connector, M12, 5-pin, field attachable

### Features

- Screw terminal connection
- Plastic locking

### Dimensions



### Technical data

#### General specifications

Number of pins	5
Connection 1	socket
Construction type 1	straight
Threading 1	M12

#### Electrical specifications

Operating voltage	$U_B$	max. 125 V AC/DC
Operating current		max. 4 A
Volume resistance		< 8 m $\Omega$

#### Ambient conditions

Ambient temperature	-40 ... 85 °C (-40 ... 185 °F)
Pollution Degree	3

#### Mechanical specifications

Protection degree	IP67
Connection	1 x M12 straight socket Screw terminals for max. 0.75 mm <sup>2</sup>

#### Material

Contacts	CuZn
Contact surface	CuSnZn
Body	PA
Slotted nut	PA
Cable	
Sheath diameter	6 ... 8 mm
Mating cycles	50

### Electrical connection

