









Model Number

NJ1,5-8GM-N

Features

- 1.5 mm flush
- Usable up to SIL2 acc. to IEC 61508

Accessories

BF 8

Mounting flange, 8 mm

Technical Data

General specifications

Switching element function		NAMUR, NC
Rated operating distance	s _n	1.5 mm
Installation		flush
Output polarity		NAMUR
Assured operating distance	sa	0 1.215 mm
Reduction factor r _{AI}		0.4
Reduction factor r _{Cu}		0.3
Reduction factor r ₃₀₄		0.85

Nominal ratings

Nominal voltage 8.2 V (R_i approx. 1 k Ω) Switching frequency Hysteresis

0... 5000 Hz 1 ... 10 typ. 5 % yes , Reverse polarity protection diode not required Suitable for 2:1 technology Current consumption

Measuring plate not detected \geq 3 mA

Measuring plate detected $\leq 1 \text{ mA}$

Ambient conditions Ambient temperature -25 ... 100 °C (-13 ... 212 °F)

Mechanical specifications

Connection type cable PVC, 2 m

Core cross-section 0.14 mm² Stainless steel 1.4305 / AISI 303 Housing material Sensing face

PBT Degree of protection IP66 / IP67

General information Use in the hazardous area see instruction manuals 1G; 2G Category

Compliance with standards and directives

Standard conformity

NAMUR EN 60947-5-6:2000 IEC 60947-5-6:1999 EN 60947-5-2:2007 Standards IEC 60947-5-2:2007

Approvals and certificates


FM approval

Control drawing 116-0165F


UL approval cULus Listed, General Purpose CSA approval cCSAus Listed, General Purpose

CCC approval / marking not required for products rated ≤36 V CCC approval

Dimensions



Electrical Connection



ATEX 1G

Instruction

Device category 1G EC-Type Examination Certificate

CE marking

ATEX marking

Directive conformity

Standards

Appropriate type

Effective internal capacitance Ci Effective internal inductance Li

Cable length

Explosion group IIC

General

Ambient temperature

Installation, Comissioning

Maintenance

Specific conditions

Protection from mechanical danger

Electrostatic charging

Manual electrical apparatus for hazardous areas

for use in hazardous areas with gas, vapour and mist PTB 00 ATEX 2048 X

€0102

⟨ы⟩ II 1G Ex ia IIC T6 Ga

EN 60079-0:2009, EN 60079-11:2012, EN 60079-26:2007 Ignition protection "Intrinsic safety"

Use is restricted to the following stated conditions

NJ 1,5-8GM-N..

≤30 nF; a cable length of 10 m is considered.

 \leq 50 μ H; a cable length of 10 m is considered.

Dangerous electrostatic charges on the fixed connection cable must be taken into account for lengths equal to and exceeding the following values:

The apparatus has to be operated according to the appropriate data in the data sheet and in this instruction manual

The EC-Type Examination Certificate has to be observed. The special conditions

Directive 94/9/EG and hence also EC-Type Examination Certificates apply in general $\frac{1}{2}$ only to the use of electrical apparatus under atmospheric conditions

The use in ambient temperatures of > 60 °C was tested with regard to hot surfaces by the mentioned certification authority.

If the equipment is not used under atmospheric conditions, a reduction of the permissible minimum ignition energies may have to be taken into consideration

The temperature ranges, according to temperature class, are given in the EC-Type Examination Certificate. Note: Use the temperature table for category 1 !!! The 20 %reduction in accordance with EN 1127-1:2007 has already been accounted for in the temperature table for category 1.

Laws and/or regulations and standards governing the use or intended usage goal must be observed.

The intrinsic safety is only assured in connection with an appropriate related apparatus and according to the proof of intrinsic safety.

The associated apparatus must satisfy the requirements of category ia.

Due to the possible danger of ignition, which can arise due to faults and/or transient currents in the equipotential bonding system, galvanic isolation of the power supply and signal circuit is preferable. Associated apparatus without electrical isolation must only be used if the appropriate requirements of IEC 60079-14 are met.

No changes can be made to apparatus, which are operated in hazardous areas. Repairs to these apparatus are not possible.

When used in the temperature range below -20 $^{\circ}\text{C}$ the sensor should be protected from knocks by the provision of an additional housing.

Electrostatic charges on the metal housing components must be avoided. Dangerous electrostatic charges on the metal housing components can be avoided by incorporating these components in the equipotential bonding.

2

ATEX 2G

Instruction

Device category 2G

EC-Type Examination Certificate CE marking

ATEX marking

Directive conformity Standards

Appropriate type

Effective internal capacitance C_i Effective internal inductance L_i

General

Ambient temperature

Installation, Comissioning

Maintenance

Specific conditions

Protection from mechanical danger

Electrostatic charging

Manual electrical apparatus for hazardous areas

for use in hazardous areas with gas, vapour and mist PTB 00 ATEX 2048 X $\mbox{\bf C}\ \mbox{\bf C}\ \mbox{\bf C}\ \mbox{\bf O}102$

⟨ы⟩ II 1G Ex ia IIC T6 Ga

94/9/FG

EN 60079-0:2009, EN 60079-11:2012 Ignition protection "Intrinsic safety" Use is restricted to the following stated conditions

NJ 1,5-8GM-N..

≤ 30 nF; a cable length of 10 m is considered.

 $\leq 50~\mu H$; a cable length of 10 m is considered.

The apparatus has to be operated according to the appropriate data in the data sheet and in this instruction manual. The EC-Type Examination Certificate has to be observed. The special conditions must be adhered to!

Directive 94/9/EG and hence also EC-Type Examination Certificates apply in general only to the use of electrical apparatus under atmospheric conditions.

The use in ambient temperatures of > 60 °C was tested with regard to hot surfaces by the mentioned certification authority.

If the equipment is not used under atmospheric conditions, a reduction of the permissible minimum ignition energies may have to be taken into consideration.

The temperature ranges, according to temperature class, are given in the EC-Type Examination Certificate.

Laws and/or regulations and standards governing the use or intended usage goal must be observed. The intrinsic safety is only assured in connection with an appropriate related apparatus and according to the proof of intrinsic safety. The sensor must be protected from strong electromagnetic fields.

No changes can be made to apparatus, which are operated in hazardous areas. Repairs to these apparatus are not possible.

When used in the temperature range below -20 $^{\circ}\text{C}$ the sensor should be protected from knocks by the provision of an additional housing.

Electrostatic charges must be avoided on the mechanical housing components. Dangerous electrostatic charges on the mechanical housing components can be avoided by incorporating these in the equipotential bonding.