




0.44 ±0.03







TECHNICAL CHARACTERISTICS

SPECIFICATION

>Contact Rating:

Switching: 25mA, 24VDC Non-Switching: 100mA, 50VDC

>Contact Resistance:

Initial: 50mOHM max.
After Life Test: 100mOHM max.
>Insulation Resistance: min. 100MOHM at 500VDC
>Dielectric Strength: 300VAC for 1 minute
>Operating Force: 500g max.
>Mechanical Life: min. 2000 cycles
>Electrical Life: 1000 cycles / 25mA, 24VDC

>Flat Actuator with top tape sealed

MATERIAL

>Cover: PPS UL 94V-0, color Black >Base: PPS UL 94V-0, color Black

>Actuator: PA 46 UL HB, color White >Contact: Gold Plated >Terminal: Gold Plated

SOLDERING INFORMATION

>Terminal in SMD version

>Reflow Soldering according to JEDEC J-STD 020 Hot Air 3 cycles max.

>Keep in "off" position during soldering

>For cleaning or washing only with top tape sealed >VPH Heating Process only with top taped sealed

WASHABLE DEFINITION

Please do not submerse washable products into water or cleaning agents or put them in locations exposed to water or liquids completely. When cleaning by hand (brushing), please do not use excessive force on our switch to avoid malfunction afterwards, because you could deform function relevant areas or you could damage sealing functions. Do not clean washable series immediately after soldering. The cleaning agent may be absorbed into the switch through respiration while the switch cools.

ENVIRONMENTAL:

>Storage condition: -40°C ~ +85°C >Operating condition: -40°C ~ +85°C

>Compliance: Lead Free, ROHS, Reach

PACKAGING INFORMATION

>Tape & Reel packaging Scale - 3:1 >On delivery in "off" position

No.Of Pole	1	2	3
Dim. A (mm)	2.31	3.58	4.85
No.Of Pole	4	5	6
Dim. A (mm)	6.12	7.39	8.66
No.Of Pole	8	10	12
Dim. A (mm)	11.20	13.74	16.28

DIMENSION

This electronic component is designed and developed with the intention for use in general electronics equipments.

0.7

Before incorporating the components into any equipments in the field such as aerospace, aviation, nuclear control, submarine, transportation, (automotive control, train control, ship control), transportation signal, disaster prevention, medical, public information network etc. where higher safety and reliability are especially required or if there is possibility of direct damage or injury to human body, Wurth Elektronik must be asked for a written approval.

In addition, even electronic component in general electronic equipments, when used in electrical circuits that require high safety, reliability functions or performance, the sufficient reliability evaluation-check for the safety must be performed before by the user before usage.

								•	•		(
n			Projection			GENERAL TOLERANCE		Basic mate	erial			
	WÜRTH ELEKTRONIK				.x = +/- 0.2 .xx = +/- 0.15							
٦,						Date	Name	DESCRIPT	TION			
					Drawn	09-02-25	Jelisarow	WS-DISV.	SMD version			
					Checked 09-02-27 Hsu Mei-Ting flat actuator with top tape sealed							
	d	Revised MatchCode	14-07-23	AL				ar aotaato	· ······ top tape of			
	С	dimension 6,9+/-0,3	14-01-31	DaF	WE Würth Elektronik		Scale	3:1	Position	n	SIZE	
	b	warning text	11-10-26	WJ	/eiCan	eiCan			-		SIZI	
	а	Actuator: HB was 94V-0	11-08-26	WJ	(CAD) eiCan		Drawing No. 4161311608xx			A4		
	REV	FILE	DATE	BY	EDV NO 4161311608xx.dft			System :Solid Edge V20				
			_			_	_				-	