





CE

Model Number

GLV18-6/25/102/115


Retroreflective sensor with 2 m fixed cable

Features

- Efficient Line in a short M18 plastic ٠ housing for standard applications
- Very high detection range ٠
- 4 LEDs indicator for 360° visibility
- · Optimized potentiometer design for a clear control button layout in the application
- Version with front optical face
- DC voltage version ٠


Product information

The GLV/GLK18 series sensors help improve the efficiency of machines and systems. The design of the M18 plastic housing, the connection technology, and sensor properties are highly standardized. Concentrating on the key sensor requirements has produced a robust and reliable product series for DC and AC/DC voltage systems without any overengineering. The mounting set included in the scope of delivery and the optimized potentiometer design ensure fast assembly and easy configuration.






Electrical connection





Indicators/operating means



1	Operating display	green
2	Signal display	yellow
4	Emitter	
5	Receiver	

Subject to modifications without notice Pepperl+Fuchs Group www.pepperl-fuchs.com

USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com

Germany: +49 621 776-4411 fa-info@pepperl-fuchs.com

Copyright Pepperl+Fuchs Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com



General specifications Effective detection range Reflector distance Threshold detection range Reference target Light source Light type Diameter of the light spot Angle of divergence Optical face Ambient light limit		0 6.5 m 0.05 6.5 m 8 m reflector C110-2 LED modulated visible red light , 640 nm approx. 300 mm at 8 m
Reflector distance Threshold detection range Reference target Light source Light type Diameter of the light spot Angle of divergence Optical face		0.05 6.5 m 8 m reflector C110-2 LED modulated visible red light , 640 nm
Threshold detection range Reference target Light source Light type Diameter of the light spot Angle of divergence Optical face		8 m reflector C110-2 LED modulated visible red light , 640 nm
Reference target Light source Light type Diameter of the light spot Angle of divergence Optical face		reflector C110-2 LED modulated visible red light , 640 nm
Light source Light type Diameter of the light spot Angle of divergence Optical face		LED modulated visible red light , 640 nm
Light type Diameter of the light spot Angle of divergence Optical face		modulated visible red light , 640 nm
Diameter of the light spot Angle of divergence Optical face		-
Angle of divergence Optical face		approx. 300 mm at 8 m
Optical face		
•		approx. 2 °
		frontal
		30000 Lux
Functional safety related parame	eters	
MTTF _d		920 a 20 a
Mission Time (T _M) Diagnostic Coverage (DC)		0 %
		0 /8
Indicators/operating means		LED groop, statically lit Power on
Operating display		LED green, statically lit Power on LED yellow: lights up when receiving the light beam ; flashes
Function display		when falling short of the stability control; OFF when light beam is interrupted
Electrical specifications		
Operating voltage	UB	10 30 V DC
No-load supply current I ₀		< 20 mA
Output		
Switching type		light on
Signal output		1 NPN, short-circuit protected open collector
Switching voltage		max. 30 V DC
Switching current		max. 100 mA
Voltage drop	U _d f	≤ 1.5 V DC 500 Hz
Switching frequency Response time	1	≤ 1 ms
Ambient conditions		2 1 113
Ambient temperature		-25 60 °C (-13 140 °F)
Storage temperature		-40 70 °C (-40 158 °F)
Mechanical specifications		-40 70 0 (-40 130 1)
Protection degree		IP67
Connection		2 m fixed cable
Material		
Housing		PC
Optical face		PMMA
Cable		PVC
Mass		approx. 75 g
Compliance with standards and ves	directi	
Standard conformity		
Product standard		EN 60947-5-2:2007
		IEC 60947-5-2:2007
Approvals and certificates		
Protection class		II, rated insulation voltage \leq 250 V AC with pollution degree
		1-2 according to IEC 60664-1
UL approval		cULus Listed, Class 2 Power Source
		Products with a maximum operating voltage of ≤36 V do not

Accessories

CPZ18B03 Mounting Bracket with swivel nut

3F 18 Mounting flange, 18 mm

BF 18-F

Mounting flange with dead stop, 18 mm

BF 5-30

Universal mounting bracket for cylindrical sensors with a diameter of 5 ... 30 mm


Other suitable accessories can be found at vww.pepperl-fuchs.com


Germany: +49 621 776-4411 fa-info@pepperl-fuchs.com

Copyright Pepperl+Fuchs Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com



Curves/Diagrams





Subject to modifications without notice Pepperl+Fuchs Group

Pepperl+Fuchs Group USA: +1 www.pepperl-fuchs.com fa-info@us.p

