




- Extended load life of 5000 hours at +105°C, with 7mm height.
- Compliant to the RoHS directive (2011/65/EU).






■Specifications

Item	Performance Characteristics											
Category Temperature Range	-40 to +105°C											
Rated Voltage Range	6.3 to 50V											
Rated Capacitance Range	0.1 to 220µF											
Capacitance Tolerance	±20% at 120Hz, 20°C											
Leakage Current	After 2 minutes' application of rated voltage at 20°C, leakage current is not more than 0.01CV or 3(µA), whichever is greater.											
						Measu	ement frequ	iency :	120Hz, Temp	erature : 20°C)	
Tangent of loss angle (tan δ)	Rated voltage (V)	6.3	1	0	16		25		35	50		
	tan δ (MAX.)	0.24	0.2	21	0.18	3	0.15		0.13	0.12		
	Measurement frequency : 120Hz											
Chability at Law Tarras and was	Rated vo	Rated voltage (V)		6.3	1	0	16	25	35	50		
Stability at Low Temperature	Impedance ratio	Z-25°C / Z+20°C		4		3	2	2	2	2		
	ZT / Z20 (MAX.)	Z-40°C / Z+20°C		8		6	4	3	3	3		
									11000			
Endurance	The specifications listed at right shall be met when					Capacitance change			Within ±30% of the initial capacitance value			
	the capacitors are restored to 20°C after the rated					tan δ			300% or less than the initial specified value			
	voltage is applied for 5000 hours at 105°C. Leakage current Less than or equal to the initial specified value											
Shelf Life	After storing the capacitors under no load at 105°C for 1000 hours and then performing voltage treatment based on JIS C 5101-4 clause 4.1 at 20°C, they shall meet the specified values for the endurance characteristics listed above.											
Marking	Printed with silver color letter on dark brown sleeve.											


■Radial Lead Type





				(mm)
φD	4	5	6.3	8
Р	1.5	2.0	2.5	3.5
φd	0.45	0.45	0.45	0.5

Type numbering system (Example: 10V 33μF)



ooimgaraac	••
φD	Pb-free leadwire Pb-free PET sleeve
4 to 8	FD

■ Dimensions

	V	6.3		10		16		25		35		50	
Cap.(μF)	Code	0J		1A		1C		1E		1V		1H	
0.1	0R1						 					4 × 7	1.0
0.22	R22		i		İ		İ					4 × 7	2.3
0.33	R33		1		 		[[l I			4×7	3.5
0.47	R47											4 × 7	5.0
1	010		<u>i</u>		i i		İ					4×7	10
2.2	2R2		!		l I		! !		! !			4 × 7	19
3.3	3R3				 							4×7	24
4.7	4R7		į		i		į			4 × 7	24	5 × 7	29
10	100		1		 	4 × 7	29	5×7	33	5 × 7	36	6.3 × 7	44
22	220	4×7	34	5 × 7	38	5 × 7	44	6.3 × 7	51	6.3 × 7	57	8 × 7	65
33	330	5×7	42	5 × 7	47	6.3 × 7	57	6.3 × 7	63	8 × 7	72		İ
47	470	5×7	50	6.3 × 7	l 59	6.3 × 7	68	8 × 7	78				1
100	101	6.3 × 7	77	8 × 7	96	8 × 7	107					Case size	Rated
220	221	8 × 7	130		İ		İ					φD×L (mm)	ripple

• Frequency coefficient of rated ripple current

Trequency decinorant or rated rippie carrent									
Frequency	50 Hz	120 Hz	300 Hz	1 kHz	10 kHz or more				
Coefficient	0.70	1.00	1 17	1.36	1.50				

Rated ripple current (mArms) at 105 $^{\circ}\text{C}$ 120Hz

Please refer to page 20, 21, 22 about the formed or taped product spec. Please refer to page 4 for the minimum order quantity.