

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [22-55-2102](#)
Status: **Active**
Overview: [SL™ Modular Connectors](#)
Description: 2.54mm Pitch SL™ Crimp Housing, Dual Row, Version B, Polarized, 10 Circuits

Documents:

| | |
|--|--|
| 3D Model | Product Specification PS-70400 (PDF) |
| Drawing (PDF) | Test Summary TS-70058-001 (PDF) |
| Product Specification PS-70058 (PDF) | RoHS Certificate of Compliance (PDF) |

Agency Certification

| | |
|-----|---------|
| CSA | LR19980 |
| UL | E29179 |

General

| | |
|----------------|--|
| Product Family | Crimp Housings |
| Series | 70450 |
| Application | Signal, Wire-to-Board |
| Comments | Version B |
| Overview | SL™ Modular Connectors |
| Product Name | SL™ |
| UPC | 800753588707 |

Physical

| | |
|-------------------------------|-----------------|
| Breakaway | No |
| Circuits (maximum) | 10 |
| Color - Resin | Black |
| Flammability | 94V-0 |
| Gender | Female |
| Glow-Wire Compliant | No |
| Material - Resin | Polyester |
| Net Weight | 0.880/g |
| Number of Rows | 2 |
| Packaging Type | Bag |
| Panel Mount | No |
| Pitch - Mating Interface | 2.54mm |
| Stackable | No |
| Temperature Range - Operating | -40°C to +105°C |

Material Info

| | |
|-----------------|------------|
| Old Part Number | 70450-0053 |
|-----------------|------------|

Reference - Drawing Numbers

| | |
|-----------------------|--------------------|
| Product Specification | PS-70058, PS-70400 |
| Sales Drawing | SD-70450-0050-0075 |
| Test Summary | TS-70058-001 |



EU RoHS

ELV and RoHS Compliant
REACH SVHC Contains SVHC: No
Low-Halogen Status Not Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[70450Series](#)

Mates With

[2.54mm Pitch C-Grid® Header 70229](#) ,
[70280](#) , [70246](#) , [70247](#)

Use With

[70058](#) , [71851](#)