

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **39-00-0075**  
**Status:** **Active**  
**Overview:** Mini-Fit Jr.™ Power Connectors  
**Description:** Mini-Fit® Male Crimp Terminal, Brass, Gold (Au) Contact Plating, Lead-free, 18-24 AWG, Reel

**Documents:**

[Drawing \(PDF\)](#) [Test Summary TS-5556-002 \(PDF\)](#)  
[Product Specification PS-5556-002 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Packaging Specification PK-5558-001 \(PDF\)](#)

**General**

Product Family	Crimp Terminals
Series	5558
Application	Power
Crimp Quality Equipment	Yes
Overview	<a href="#">Mini-Fit Jr.™ Power Connectors</a>
Packaging Alternative	<a href="#">39-00-0076 (Loose)</a>
Product Name	Mini-Fit®
UPC	800754394093

**Physical**

Durability (mating cycles max)	30
Gender	Male
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	0.126/g
Packaging Type	Reel
Plating min - Mating	0.381µm
Plating min - Termination	2.032µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.30-3.10mm
Wire Size AWG	18, 20, 22, 24
Wire Size mm²	N/A

**Electrical**


Current - Maximum per Contact	9.0A
Voltage - Maximum	600V

**Material Info**

Old Part Number	5558GS4
-----------------	---------

**Reference - Drawing Numbers**

Packaging Specification	PK-5558-001
Product Specification	PS-5556-002
Sales Drawing	SD-5558-002
Test Summary	TS-5556-002



**EU RoHS**

**ELV and RoHS  
Compliant**

**REACH SVHC**

Not Reviewed

**Low-Halogen Status**

**Low-Halogen**

**China RoHS**



**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

[5558Series](#)

**Mates With**

[5556 Mini-Fit® Crimp Terminal](#)

**Use With**

[5559 Mini-Fit Jr.™ Plug Housing](#)

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

Description	Product #
Extraction Tool	<a href="#">0011030044</a>
Hand Crimp Tool for Male and Female Crimp Terminals, 16-24 AWG Wire	<a href="#">0638190900</a>
FineAdjust™ Applicator for Insulation OD	<a href="#">0639002600</a>

2.50-2.95mm, 18-24 AWG Wire FineAdjust™ Applicator for Insulation OD	<u>0639002900</u>
1.65-2.05mm, 18-24 AWG Wire FineAdjust™ Applicator for Insulation OD	<u>0639015600</u>
1.90-2.30mm - 18-24 AWG FineAdjust™ Applicator for Insulation OD	<u>0639023900</u>
1.40-1.70mm - 18-24 AWG FineAdjust™ Applicator for Insulation OD	<u>0639024800</u>
2.50-2.95mm Optimized for 18 AWG Only FineAdjust™ Applicator for Insulation OD	<u>0639024900</u>
2.30-2.60mm - 18-24 AWG T2 Terminator™ for insulation OD	<u>0639102600</u>
2.50-2.95mm - 18-24 AWG T2 Terminator™ for insulation OD 1.65 – 2.05mm – 18 – 24	<u>0639102900</u>
AWG T2 Terminator™ for insulation OD	<u>0639115600</u>
1.90-2.30mm - 18-24 AWG T2 Terminator™ for insulation OD	<u>0639123900</u>
1.40-1.70mm - 18-24 AWG T2 Terminator™ for insulation OD	<u>0639124800</u>
2.50-2.95mm optimized for 18 AWG only T2 Terminator™ for insulation OD	<u>0639124900</u>
2.30-2.60mm - 18-24 AWG	

This document was generated on 04/17/2015

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**