MITI-3V1 Features and Benefits

Features

- Ultra-miniature normally open switch with 7.00mm x 1.80mm (0.276" x 0.071") gass envelope
- Capable of switching 170Vdc at up to 10 Watts
- 1012 Ohms insulation resistance
- Available sensitivity range
- Surface mount version available


Benefits

- Her metically sealed switch contacts are not effected by and have no effect on their external environment
- Low, stable contact resistance
- Very low space requirement
- Zero operating power required for contact dosure
- Fit and forget durability

Applications

- Reed relays
- Security
- Metering
- Mobile phones

DIMENSIONS (in) mm



Switch Type	MITI-3V1					
Contact Form	A					
ELECTRICAL RATINGS						

Contact Rating (1)		Watt - max.	10
Voltage	Switching	Vdc - max.	170
	Breakdown	Vdc - min.	175
Current	Switching	A - max.	0.25
	Carry	A - max.	0.5
Resistance	Contact, Initial	Ω - max.	0.15
	Insulation	Ω - min.	1012
Capacitance	Contact	pF - typ.	0.3
Temperature	Operating	°C	-40 to +125
	Storage (5)	°C	-65 to +125

OPERATING CHARACTERISTICS

Operate Time (2)		ms - max.	0.45
Release Time (2)		ms - max.	0.2
Shock	11ms ½ sine wave	G - max.	150
Vibration	50-2000 Hertz	G - max.	30
Resonant Frequency		Hz - typ.	18000

MAGNETIC CHARACTERISTICS

Pull-In Range (3)		Ampere Turns	6-10		
Rating Sensitivity (4)		Ampere Turns	12		
Test Coil			L4991		

Notes

- Contact rating-Product of the switching voltage and current should never exceed the wattage rating. Contact Hamlin for additional load/life information.
 Operate (inc. bounce) /Release Time-per BA/NARM RS421A, diode suppressed coil.
- 3) Pull in Range-Contact Hamlin for tolerances available within this range.
- 4) Rating Sensitivity-The value at which contact ratings and operating characteristics are

determined. Derating may be required below this value.

Sorage Temperature-Long time exposure at elevated temperature may degrade solderability of the leads

Hamlin USA Tel: +1 920 648 3000 • Fax: +1 920 648 3001 • Email: sales.us@hamlin.com Tel: +44 (0)1379 649700 • Fax: +44 (0)1379 649702 • Email: sales.uk@hamlin.com Hamlin UK Tel: +86 (0) 512 69365 800 • Fax: +86 (0) 512 69365 811 • Email: sales.on@hamlin.com

Issue No: AC Date: 9/24/13 DCR: B9891

DETAILS/PROVIDED ON THISDATA SHEET ARE-PROVIDED FOR INFORMATION RUPPO \$50 NIX AND \$10 ULD NOT BE-RELIED UPON ASBEING ACCURATE FOR ANY FARTICULAR RUPPOSE. Product performance may be affected by the application to which the product is applied. Upon request, HAMLIN will assist pur drasers by providing information specific to any particular application. HAMLIN distains any and all liability whatevener for any purforms is relative upon the information contained on this data sheet without further consultation with authorised representatives of HAMLIN.