

## High Current Axial Plastic Rectifier


**P600**

### FEATURES

- Low forward voltage drop
- Low leakage current,  $I_R$  less than 0.1  $\mu$ A
- High forward current capability
- High forward surge capability
- Solder dip 275 °C max. 10 s, per JESD 22-B106
- Material categorization: For definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)


**RoHS**  
COMPLIANT

### TYPICAL APPLICATIONS

For use in general purpose rectification of power supplies, inverters, converters, and freewheeling diodes application.

#### Note

- These devices are not AEC-Q101 qualified.

### MECHANICAL DATA

**Case:** P600, void-free molded epoxy body  
Molding compound meets UL 94 V-0 flammability rating  
Base P/N-E3 - RoHS-compliant, commercial grade

**Terminals:** Matte tin plated leads, solderable per J-STD-002 and JESD 22-B102

E3 suffix meets JESD 201 class 1A whisker test

**Polarity:** Color band denotes cathode end

PRIMARY CHARACTERISTICS	
$I_{F(AV)}$	6.0 A
$V_{RRM}$	50 V, 100 V, 200 V, 400 V, 600 V, 800 V
$I_{FSM}$	400 A
$I_R$	5.0 $\mu$ A
$V_F$	0.9 V, 0.95 V
$T_J$ max.	150 °C
Package	P600
Diode variations	Single die

MAXIMUM RATINGS ( $T_A = 25$ °C unless otherwise noted)								
PARAMETER	SYMBOL	GI750	GI751	GI752	GI754	GI756	GI758	UNIT
Maximum repetitive peak reverse voltage	$V_{RRM}$	50	100	200	400	600	800	V
Maximum RMS voltage	$V_{RMS}$	35	70	140	280	420	560	V
Maximum DC blocking voltage	$V_{DC}$	50	100	200	400	600	800	V
Maximum non-repetitive peak reverse voltage	$V_{RSM}$	60	120	240	480	720	1200	V
Maximum average forward rectified current at	$T_A = 60$ °C, PCB mounting (fig. 1)	6.0						A
	$T_L = 60$ °C, 0.125" (3.18 mm) lead length (fig. 2)	22						
Peak forward surge current 8.3 ms single half sine-wave superimposed on rated load	$I_{FSM}$	400						A
Operating junction and storage temperature range	$T_J, T_{STG}$	- 50 to + 150						°C

ELECTRICAL CHARACTERISTICS ( $T_A = 25$ °C unless otherwise noted)									
PARAMETER	TEST CONDITIONS	SYMBOL	GI750	GI751	GI752	GI754	GI756	GI758	UNIT
Maximum instantaneous forward voltage at	6.0 A	$V_F$	0.90				0.95		V
	100 A		1.25				1.30		
Maximum DC reverse current at rated DC blocking voltage	$T_A = 25$ °C	$I_R$	5.0						$\mu$ A
	$T_A = 100$ °C		1.0						mA
Typical reverse recovery time	$I_F = 0.5$ A, $I_R = 1.0$ A, $I_{rr} = 0.25$ A	$t_{rr}$	2.5						$\mu$ s
Typical junction capacitance	4.0 V, 1 MHz	$C_J$	150						pF



THERMAL CHARACTERISTICS ( $T_A = 25\text{ }^\circ\text{C}$ unless otherwise noted)								
PARAMETER	SYMBOL	GI750	GI751	GI752	GI754	GI756	GI758	UNIT
Typical thermal resistance	$R_{\theta JA}^{(1)}$	20						$^\circ\text{C/W}$
	$R_{\theta JL}^{(1)}$	4.0						

**Note**

(1) Thermal resistance from junction to ambient and from junction to lead at 0.375" (9.5 mm) lead length, PCB mounted with 1.1" x 1.1" (30 mm x 30 mm) copper pads

ORDERING INFORMATION (Example)				
PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE
GI756-E3/54	2.1	54	800	13" diameter paper tape and reel
GI756-E3/73	2.1	73	300	Ammo pack packaging

**RATINGS AND CHARACTERISTICS CURVES ( $T_A = 25\text{ }^\circ\text{C}$  unless otherwise noted)**



Fig. 1 - Maximum Forward Current Derating Curve




Fig. 3 - Maximum Peak Forward Surge Current




Fig. 2 - Maximum Forward Current Derating Curve




Fig. 4 - Typical Instantaneous Forward Characteristics



Fig. 5 - Typical Reverse Characteristics




Fig. 6 - Typical Transient Thermal Impedance

**PACKAGE OUTLINE DIMENSIONS** in inches (millimeters)





## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

## Material Category Policy

**Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.**

**Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.**

**Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.**