

This document was generated on 03/04/2015

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 43045-0601

Status: Active

Overview: Micro-Fit 3.0TM Connectors

Description: Micro-Fit 3.0™ Header, Surface Mount Compatible, Dual Row, Right Angle, with Snap-

in Plastic Peg PCB Lock, 6 Circuits, 0.38µm Gold (Au) Selective Plating, Glow Wire

Compatible

Documents:

3D Model Test Summary TS-43045-002 (PDF)
Drawing (PDF) RoHS Certificate of Compliance (PDF)

Product Specification PS-43045 (PDF) Product Literature (PDF)

Test Summary TS-43045-001 (PDF)

Agency Certification

CSA LR19980 TUV R72081037 UL E29179

General

Product Family PCB Headers Series 43045

Application Power, Wire-to-Board

Comments

"High Temperature|Square Pin|Solder Type<P><P>This
Molex product is manufactured from material that has
the following ratings, tested by independent agencies:.

the following ratings, tested by independent agencies:.
a) A Glow Wire Ignition Temperature (GWIT) of at least 775 deg C per IEC 60695-2-13.. b) A Glow Wire Flammability Index (GWFI) above 850 deg C per IEC 60695-2-12.and hence complies with the requirements set out in the International Standard IEC 60335-1 5th edition - household and similar electrical appliances - safety, section 30 Resistance to heat and fire. <P><P> The customers using this product must determine its suitability for use in their particular application through testing or other acceptable means as described in end-product glow-wire flammability test standard IEC 60695-2-11 and any applicable product end-use standard(s). <P> If it is determined during the customer's evaluation of suitability, that higher

performance is required, please contact Molex for

possible product options."

Overview <u>Micro-Fit 3.0™ Connectors</u>


 Product Literature Order No
 987650-5984

 Product Name
 Micro-Fit 3.0™

 UPC
 800754370868

Physical

Breakaway No Circuits (Loaded) 6 Circuits (maximum) 6 Color - Resin Black Durability (mating cycles max) 30 Flammability 94V-0 Glow-Wire Compliant Yes Mated Height 10.29mm Material - Metal **Brass**



EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen



Need more information on product environmental compliance?

Email <u>productcompliance@molex.com</u>
For a multiple part number RoHS Certificate of Compliance, click here

Please visit the <u>Contact Us</u> section for any non-product compliance questions.

Search Parts in this Series

43045 Series

Mates With

43025 Micro-Fit 3.0™ Receptacle Housing

Material - Plating Mating Gold Material - Plating Termination Tin

Material - Resin High Temperature Thermoplastic

Net Weight 1.106/g Number of Rows 2

Orientation Right Angle

PCB Locator Yes **PCB** Retention Yes PCB Thickness - Recommended 1.60mm Packaging Type Tray Pitch - Mating Interface 3.00mm Plating min - Mating 0.381µm Polarized to PCB Yes Shrouded Fully Stackable No Surface Mount Compatible (SMC) Yes

Temperature Range - Operating -40°C to +105°C Termination Interface: Style Through Hole

Electrical

Current - Maximum per Contact 5A Voltage - Maximum 600V

Solder Process Data

Duration at Max. Process Temperature (seconds) 30

Lead-free Process Capability SMC & Wave Capable (TH only)

Max. Cycles at Max. Process Temperature 3
Process Temperature max. C 260

Material Info

Reference - Drawing Numbers

Product Specification PS-43045, RPS-43045-003, RPS-43045-004

Sales Drawing SD-43045-001

Test Summary TS-43045-001, TS-43045-002

This document was generated on 03/04/2015

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION