


UNCONTROLLED DOCUMENT







PART NUMBER	SSL-LX5093HD-5V	REV.	D
DATE	E.C.N. NUMBER AND REVISION COMMENTS		REV.
02.10.95	UPDATED SPECS.		Α
05.25.01	E.C.N. #10BRDR. & REDRAWN.		В
10.19.06	E.C.N. #11148.		С
02.08.12	E.C.N. #10BRDR. & REDRAWN.		D

ELECTRO-OPTICAL CHARACTERISTICS Ta=25°C If=5V PARAMETER TYP UNITS TEST COND PEAK WAVELENGTH 700 FORWARD VOLTAGE 5.0 7.0 Vf REVERSE VOLTAGE 5.0 ۷r Ir=100µA AXIAL INTENSITY 3 If=5V mcd VIEWING ANGLE 60 2x theta EMITTED COLOR: RED EPOXY LENS FINISH: RED DIFFUSED

LIMITS OF SAFE OPERATION AT 25°C		
PARAMETER	MAX	UNITS
PEAK FORWARD VOLTAGE	7.0	٧
STEADY CURRENT	12	mA
POWER DISSIPATION	310	mW
DERATE FROM 25°C	-1.2	mW/*C
OPERATING TEMP.	-40 TO +85	•C
STORAGE TEMP.	-40 TO +85	•C
SOLDERING TEMP.	+260	•C
2.0mm FROM BODY	3	SEC.

*UNLESS OTHERWISE SPECIFIED TOLERANCES PER DECIMAL PRECISION ARE: X=±1 (±0.039), X.X=±0.5 (±0.020), X.XX=±0.25 (±0.010), X.XXX=±0.127 (±0.005). LEAD SIZE=±0.05 (±0.002), LEAD LENGTH=±0.75 (±0.030). MIN= $^{+0.00}_{-0.00}$ PRECISION MAX.= $^{+0.00}_{-0.00}$ PRECISION $^{-0.00}_{-0.00}$ MAX.= $^{+0.00}_{-0.00}$ PRECISION $^{-0.00}_{-0.00}$ PRECISION $^{-0.00}_{-0$ UNCONTROLLED DOCUMENT



290 E. HELEN ROAD PALATINE, IL 60067-6976 PHONE: +1.847.359.2790 FAX: +1.847.359.6538 WEB: WWW.LUMEX.COM MEMBER OF ITW PHOTONICS GROUP QUASARBRITE T-5mm (T-1 3/4) 700nm RED LED, RED DIFFUSED LENS, 5 VOLT OPERATION.

THE SPECIFICATIONS MAY CHANGE AT ANY TIME WITHOUT NOTICE DUE TO NEW MATERIALS OR PRODUCT IMPROVEMENT.

CONFIDENTIAL INFORMATION
THE INFORMATION CONTAINED IN THIS DOCUMENT IS THE PROPERTY OF LUMEX INC. EXCEPT AS SPECIFICALLY AUTHORIZED IN WRITING BY LUMEX INC., THE HOLDER OF THIS DOCUMENT SHALL KEEP ALL INFORMATION CONTAINED HEREIN CONFIDENTIAL AND SHALL PROTECT SAME IN WHOLE OR IN PART FROM DISCLOSURE AND DISSEMINATION TO ALL THIRD PARTIES.

DATE: 02.01.12 DRAWN BY: AΒ PAGE: 1 OF 1 CHKD BY: KF SCALE: NTS APRVD BY: KF UNIT: mm [INCH] (Pb)