

This document was generated on 03/02/2015

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 43045-0611

Status: **Active**

Micro-Fit 3.0™ Connectors **Overview:**

Micro-Fit 3.0™ Header, Surface Mount, Dual Row, Right Angle, with Solder Tab, 6 **Description:**

Circuits, 0.76µm Gold (Au) Selective Plating, Glow Wire Compatible

Documents:

Drawing (PDF) Test Summary TS-43045-002 (PDF) 3D Model RoHS Certificate of Compliance (PDF)

Product Literature (PDF) Product Specification PS-43045 (PDF)

Test Summary TS-43045-001 (PDF)

Agency Certification

CSA LR19980 TUV R72081037 UL E29179

General

Product Family PCB Headers Series 43045

Application Power, Wire-to-Board

"High Temperature|Square Pin|Solder Type<P><P>This Comments

Molex product is manufactured from material that has the following ratings, tested by independent agencies:. a) A Glow Wire Ignition Temperature (GWIT) of at least 775 deg C per IEC 60695-2-13.. b) A Glow Wire Flammability Index (GWFI) above 850 deg C per IEC 60695-2-12.and hence complies with the requirements set out in the International Standard IEC 60335-1 5th edition - household and similar electrical appliances - safety, section 30 Resistance to heat and fire. <P><P> The customers using this product must determine its suitability for use in their particular application through testing or other acceptable means as described in end-product glow-wire flammability test standard IEC 60695-2-11 and any applicable product end-use standard(s). <P> If it is determined during the customer's evaluation of suitability, that higher performance is required, please contact Molex for

possible product options."

Micro-Fit 3.0™ Connectors

987650-5984 Micro-Fit 3.0™ 800754371162

Physical


Product Name

Overview

UPC

Product Literature Order No

Breakaway No Circuits (Loaded) 6 Circuits (maximum) 6 Color - Resin Black Durability (mating cycles max) 30 Flammability 94V-0 **Glow-Wire Compliant** Yes Mated Height 10.29mm Material - Metal Brass Material - Plating Mating Gold



EU RoHS ELV and RoHS Compliant **REACH SVHC Contains SVHC: No** Low-Halogen Status

Low-Halogen



Need more information on product environmental compliance?

Email productcompliance@molex.com For a multiple part number RoHS Certificate of Compliance, click here

Please visit the Contact Us section for any non-product compliance questions.

Search Parts in this Series

43045Series

Mates With

43025 Micro-Fit 3.0™ Receptacle Housing

Material - Plating Termination Tin

Material - Resin High Temperature Thermoplastic

Net Weight 1.124/g Number of Rows 2

Orientation Right Angle

PCB Locator Yes
PCB Retention Yes
PCB Thickness - Recommended 1.60mm

Packaging Type Embossed Tape on Reel

Pitch - Mating Interface 3.00mm
Plating min - Mating 0.762µm
Polarized to PCB Yes
Shrouded Fully
Stackable No
Surface Mount Compatible (SMC) N/A

Temperature Range - Operating -40°C to +105°C Termination Interface: Style Surface Mount

Electrical

Current - Maximum per Contact 5A Voltage - Maximum 600V

Solder Process Data

Duration at Max. Process Temperature (seconds) 30

Lead-free Process Capability Reflow Capable (SMT only)

Max. Cycles at Max. Process Temperature 3
Process Temperature max. C 260

Material Info

Reference - Drawing Numbers

Product Specification PS-43045, RPS-43045-003, RPS-43045-004

Sales Drawing SD-43045-004

Test Summary TS-43045-001, TS-43045-002

This document was generated on 03/02/2015

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION