


Power MOSFET

PRODUCT SUMMARY						
V _{DS} (V)	80	800				
$R_{DS(on)}(\Omega)$	V _{GS} = 10 V	6.5				
Q _g (Max.) (nC)	3	38				
Q _{gs} (nC)	5	5.0				
Q _{gd} (nC)	2	21				
Configuration	Sin	Single				



FEATURES

- Dynamic dV/dt Rating
- Repetitive Avalanche Rated
- · Fast Switching
- · Ease of Paralleling
- Simple Drive Requirements
- Compliant to RoHS Directive 2002/95/EC



DESCRIPTION

Third generation Power MOSFETs from Vishay provide the designer with the best combination of fast switching, ruggedized device design, low on-resistance and cost-effectiveness.

The TO-220AB package is universally preferred for all commercial-industrial applications at power dissipation levels to approximately 50 W. The low thermal resistance and low package cost of the TO-220AB contribute to its wide acceptance throughout the industry.

ORDERING INFORMATION			
Package	TO-220AB		
Lead (Pb)-free	IRFBE20PbF		
Lead (Fb)-liee	SiHFBE20-E3		
SnPb	IRFBE20		
SIIFU	SiHFBE20		

PARAMETER			SYMBOL	LIMIT	UNIT	
Drain-Source Voltage			V _{DS}	800	V	
Gate-Source Voltage			V _{GS}	± 20	7 v	
Continuous Drain Current	V -+ 10 V	$T_{\rm C} = 25 ^{\circ}{\rm C}$ $T_{\rm C} = 100 ^{\circ}{\rm C}$		1.8	А	
	V _{GS} at 10 V	T _C = 100 °C	ID	1.2		
Pulsed Drain Current ^a			I _{DM}	7.2		
Linear Derating Factor				0.43	W/°C	
Single Pulse Avalanche Energy ^b			E _{AS}	180	mJ	
Repetitive Avalanche Current ^a			I _{AR}	1.8	А	
Repetitive Avalanche Energy ^a			E _{AR}	5.4	mJ	
Maximum Power Dissipation T _C = 25 °C			P _D	54	W	
Peak Diode Recovery dV/dt ^c			dV/dt	2.0	V/ns	
Operating Junction and Storage Temperature Range			T _J , T _{stg}	- 55 to + 150	- °C	
oldering Recommendations (Peak Temperature) for 10 s				300 ^d		
Mounting Torque	6-32 or M3 screw			10	lbf ⋅ in	
Mounting Torque				1.1	N⋅m	

Notes

- a. Repetitive rating; pulse width limited by maximum junction temperature (see fig. 11).
- b. V_{DD} = 50 V, starting T_J = 25 °C, L = 104 mH, R_g = 25 Ω , I_{AS} = 1.8 A (see fig. 12).
- c. $I_{SD} \le 1.8 \text{ A}$, $dI/dt \le 80 \text{ A/}\mu\text{s}$, $V_{DD} \le 600$, $T_{J} \le 150 ^{\circ}\text{C}$.
- d. 1.6 mm from case.

^{*} Pb containing terminations are not RoHS compliant, exemptions may apply



THERMAL RESISTANCE RATINGS						
PARAMETER	SYMBOL	TYP.	MAX.	UNIT		
Maximum Junction-to-Ambient	R _{thJA}	-	62			
Case-to-Sink, Flat, Greased Surface	R _{thCS}	0.50	-	°C/W		
Maximum Junction-to-Case (Drain)	R _{thJC}	-	2.3			

PARAMETER	SYMBOL	TEST	MIN.	TYP.	MAX.	UNIT	
Static							
Drain-Source Breakdown Voltage	V _{DS}	$V_{GS} = 0 \text{ V}, I_D = 250 \mu\text{A}$		800	-	-	V
V _{DS} Temperature Coefficient	$\Delta V_{DS}/T_{J}$	Reference t	o 25 °C, I _D = 1 mA	-	0.98	-	V/°C
Gate-Source Threshold Voltage	V _{GS(th)}	$V_{DS} = V$	_{GS} , I _D = 250 μA	2.0	-	4.0	V
Gate-Source Leakage	I _{GSS}	V _G	_S = ± 20 V	-	-	± 100	nA
Zero Osto Vellana Buria Osmal		V _{DS} = 800 V, V _{GS} = 0 V		-	-	100	
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} = 640 V, V	_{GS} = 0 V, T _J = 125 °C	-	-	500	μA
Drain-Source On-State Resistance	R _{DS(on)}	V _{GS} = 10 V	I _D = 1.1 A ^b	-	-	6.5	Ω
Forward Transconductance	9 _{fs}	V _{DS} = 10	00 V, I _D = 1.1 A ^b	0.80	-	-	S
Dynamic				l			
Input Capacitance	C _{iss}	V 0V		-	530	-	pF
Output Capacitance	C _{oss}		$V_{GS} = 0 \text{ V},$ $V_{DS} = 25 \text{ V},$ $f = 1.0 \text{ MHz}, \text{ see fig. 5}$		150	-	
Reverse Transfer Capacitance	C _{rss}	f = 1.0 l			90	-	
Total Gate Charge	Qg			-	-	38	nC
Gate-Source Charge	Q _{gs}	V _{GS} = 10 V	$I_D = 1.8 \text{ A}, V_{DS} = 400 \text{ V},$ see fig. 6 and 13 ^b	-	-	5.0	
Gate-Drain Charge	Q_{gd}	see lig. 6 and 135		-	-	21	1
Turn-On Delay Time	t _{d(on)}	V_{DD} = 400 V, I_D = 1.8 A, R_g = 18 Ω , R_D = 230 Ω , see fig. 10 ^b		-	8.2	-	- ns
Rise Time	t _r			-	17	-	
Turn-Off Delay Time	t _{d(off)}			-	58	-	
Fall Time	t _f			-	27	-	
Internal Drain Inductance	L _D	Between lead, 6 mm (0.25") from package and center of die contact		-	4.5	-	
Internal Source Inductance	L _S			-	7.5	-	- nH
Drain-Source Body Diode Characteristic	s						
Continuous Source-Drain Diode Current	I _S	MOSFET symbol showing the integral reverse p - n junction diode		-	-	1.8	A
Pulsed Diode Forward Current ^a	I _{SM}			-	-	7.2	
Body Diode Voltage	V_{SD}	T _J = 25 °C, I _S = 1.8 A, V _{GS} = 0 V ^b		-	-	1.4	V
Body Diode Reverse Recovery Time	t _{rr}	T 05 °C !	1 0 A Al/At 100 A /:b	-	380	570	ns
Body Diode Reverse Recovery Charge	Q_{rr}	$T_J = 25 ^{\circ}\text{C}, I_F = 1.8 \text{A}, \text{dI/dt} = 100 \text{A/}\mu\text{s}^b$		-	0.94	1.4	μC
Forward Turn-On Time	t _{on}	Intrinsic turn-	-on is do	minated b	ov L _s and	L _D)	

Notes

- a. Repetitive rating; pulse width limited by maximum junction temperature (see fig. 11).
- b. Pulse width \leq 300 µs; duty cycle \leq 2 %.



TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)




Fig. 1 - Typical Output Characteristics, T_C = 25 °C




Fig. 3 - Typical Transfer Characteristics




Fig. 2 - Typical Output Characteristics, T_C = 150 °C




Fig. 4 - Normalized On-Resistance vs. Temperature






Fig. 5 - Typical Capacitance vs. Drain-to-Source Voltage




Fig. 7 - Typical Source-Drain Diode Forward Voltage




Fig. 6 - Typical Gate Charge vs. Gate-to-Source Voltage




Fig. 8 - Maximum Safe Operating Area






Fig. 9 - Maximum Drain Current vs. Case Temperature

T_C, Case Temperature (°C)




Fig. 10a - Switching Time Test Circuit




Fig. 10b - Switching Time Waveforms




Fig. 11 - Maximum Effective Transient Thermal Impedance, Junction-to-Case






Fig. 12a - Unclamped Inductive Test Circuit




Fig. 12b - Unclamped Inductive Waveforms




Fig. 12c - Maximum Avalanche Energy vs. Drain Current




Fig. 13a - Basic Gate Charge Waveform





Fig. 13b - Gate Charge Test Circuit





Peak Diode Recovery dV/dt Test Circuit







Fig. 14 - For N-Channel

Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package/tape drawings, part marking, and reliability data, see www.vishay.com/ppg?91117.






TO-220-1



	MILLIN	IETERS	INC	HES		
DIM.	MIN.	MAX.	MIN.	MAX.		
Α	4.14	4.70	0.163	0.185		
b	0.69	1.02	0.027	0.040		
b(1)	1.14	1.73	0.045	0.068		
С	0.36	0.61	0.014	0.024		
D	14.33	15.85	0.564	0.624		
Е	9.96	10.52	0.392	0.414		
е	2.41	2.67	0.095	0.105		
e(1)	4.88	5.28	0.192	0.208		
F	0.43	1.40	0.017	0.055		
H(1)	6.10	6.48	0.240	0.255		
J(1)	2.41	2.92	0.095	0.115		
L	13.36	14.40	0.526	0.567		
L(1)	3.33	4.04	0.131	0.159		
ØР	3.53	3.94	0.139	0.155		
Q	2.59	3.00	0.102	0.118		
ECN: X15-0003-Rev. A, 19-Jan-15 DWG: 6031						

Notes

- M* = 0.052 inches to 0.064 inches (dimension including protrusion), heatsink hole for HVM
- Outline conforms to JEDEC® outline TO-220AB with exception of dimension F



Revison: 19-Jan-15 1 Document Number: 66542



Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.

Revision: 02-Oct-12 Document Number: 91000