# MMCX Straight Edge Mount Jack Receptacle multicomp



## **Specifications:**

#### Electrical

Frequency Range	: DC-6GHz
Nominal Impedance	: 50Ω
Voltage Rating	: 250V Max.
VSWR	: 1.22 Max.

#### Materials

Bodies	
Centre Contact	
Insulation	


: Brass : Beryllium Copper


: PTFE


#### Environmental

**Operating Temperature Range** 

: -55°C to +155°C







RoHS

**Compliant** 

Dimensions : Millimetres (Inches)

## **Finishes and Others**

No.	Description	Material	Qty	Finish
1	Body	Brass		Gold 30µ" Min.
2	Insulation	PTFE	1	None
3	Centre Contact	Beryllium copper		Gold 3µ" Min.

## Part Number Table

Description	Part Number
MMCX Straight Edge Mount Jack Receptacle	MC000989

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage resulting from any reliance on the Information or use of it (including liability resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.

www.element14.com www.farnell.com www.newark.com

