


WXA SERIES
105°C Low profile.
◆FEATURES

- 9~25mm height.
- RoHS compliance.


◆SPECIFICATIONS

Items	Characteristics																																															
	-55~+105°C	-40~+105°C	-25~+105°C																																													
Category Temperature Range	-55~+105°C	-40~+105°C	-25~+105°C																																													
Rated Voltage Range	6.3~50V.DC	160~250V.DC	350~450V.DC																																													
Capacitance Tolerance	±20%(20°C, 120Hz)																																															
Leakage Current(MAX)	6.3~50V.DC		160~450V.DC																																													
	I=0.01CV or 3µA whichever is greater. (After 2 minutes application of rated voltage)		CV≤1000																																													
			CV>1000																																													
		I=0.1CV+40µA (1minute) I=0.03CV+15µA (5minutes)	I=0.04CV+100µA (1minute) I=0.02CV+25µA (5minutes)																																													
		I=Leakage Current(µA)	C=Capacitance(µF) V=Rated Voltage(V)																																													
Dissipation Factor(MAX) (tanδ)	Rated Voltage (V)												(20°C, 120Hz)																																			
	tanδ																																															
	<table border="1"> <tr> <td>6.3</td><td>10</td><td>16</td><td>25</td><td>35</td><td>50</td><td>160</td><td>200</td><td>250</td><td>350</td><td>400</td><td>450</td> </tr> <tr> <td>0.30</td><td>0.26</td><td>0.20</td><td>0.18</td><td>0.14</td><td>0.12</td><td>0.20</td><td>0.20</td><td>0.20</td><td>0.20</td><td>0.20</td><td>0.25</td> </tr> <tr> <td>0.26</td><td>0.22</td><td>0.18</td><td>0.16</td><td>0.14</td><td>0.12</td><td>0.20</td><td>0.20</td><td>0.20</td><td>0.20</td><td>0.20</td><td>0.25</td> </tr> </table>													6.3	10	16	25	35	50	160	200	250	350	400	450	0.30	0.26	0.20	0.18	0.14	0.12	0.20	0.20	0.20	0.20	0.20	0.25	0.26	0.22	0.18	0.16	0.14	0.12	0.20	0.20	0.20	0.20	0.20
6.3	10	16	25	35	50	160	200	250	350	400	450																																					
0.30	0.26	0.20	0.18	0.14	0.12	0.20	0.20	0.20	0.20	0.20	0.25																																					
0.26	0.22	0.18	0.16	0.14	0.12	0.20	0.20	0.20	0.20	0.20	0.25																																					
When capacitance is over 1000µF, tanδ shall be added 0.02 to the listed value with increase of every 1000µF.																																																
Endurance	After applying rated voltage with rated ripple current for 2000 hours at 105°C, the capacitors shall meet the following requirements.																																															
	Capacitance Change		Within ±25% of the initial value.																																													
	Dissipation Factor		Not more than 200% of the specified value.																																													
Leakage Current		Not more than the specified value.																																														
Low Temperature Stability Impedance Ratio(MAX)	Rated Voltage (V)												(120Hz)																																			
	Z(-25°C)/Z(20°C)																																															
	Z(-40°C)/Z(20°C)																																															
<table border="1"> <tr> <td>6.3</td><td>10</td><td>16</td><td>25</td><td>35</td><td>50</td><td>160</td><td>200</td><td>250</td><td>350</td><td>400</td><td>450</td> </tr> <tr> <td>4</td><td>3</td><td>2</td><td>2</td><td>2</td><td>2</td><td>3</td><td>3</td><td>3</td><td>6</td><td>6</td><td>6</td> </tr> <tr> <td>8</td><td>6</td><td>4</td><td>4</td><td>3</td><td>3</td><td>-</td><td>-</td><td>-</td><td>-</td><td>-</td><td>-</td> </tr> </table>													6.3	10	16	25	35	50	160	200	250	350	400	450	4	3	2	2	2	2	3	3	3	6	6	6	8	6	4	4	3	3	-	-	-	-	-	-
6.3	10	16	25	35	50	160	200	250	350	400	450																																					
4	3	2	2	2	2	3	3	3	6	6	6																																					
8	6	4	4	3	3	-	-	-	-	-	-																																					

◆MULTIPLIER FOR RIPPLE CURRENT

Frequency (Hz)		60(50)	120	500	1k	10k≤
Coefficient	1.5~6.8µF	0.65	1.0	1.20	1.30	1.50
	10~68µF	0.8	1.0	1.20	1.30	1.50
	100~1000µF	0.8	1.0	1.10	1.15	1.20
	2200~10000µF	0.8	1.0	1.05	1.10	1.15

◆OPTION

	Code
PET Sleeve	EFC

◆PART NUMBER

□□□	WXA	□□□□□	M	□□□	□□	D×L
Rated Voltage	Series	Capacitance	Capacitance Tolerance	Option	Lead Forming	Case Size

