

## 5320UL Multi-Conductor - Commercial Applications - 2 Conductors Cabled



For more Information  
please call

1-800-Belden1



### General Description:

Fire Alarm Cable, Riser-FPLR, 2-18 AWG solid bare copper conductors with polyolefin insulation, PVC jacket with ripcord

### Usage (Overall)

Suitable Applications: Fire Protections, Alarm, Signal, Monitor/Detection, Audio Circuits, Control Circuits, Initiating Circuits, Notification Circuits

### Physical Characteristics (Overall)

#### Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
2	18	Solid	BC - Bare Copper

Total Number of Conductors: 2

#### Insulation

Insulation Material:

Insulation Material	Wall Thickness (mm)
PP - Polypropylene	0.178

#### Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

#### Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (mm)
PVC - Polyvinyl Chloride	0.432

Outer Jacket Ripcord: Yes

#### Overall Cable

Overall Cabling Lay Length & Direction:

Length (m)	Direction	Twists (twist/m)
76.200	Left Hand	13.124

Overall Cabling Color Code Chart:

Number	Color
1	Black
2	Red

Overall Nominal Diameter: 3.632 mm

### Mechanical Characteristics (Overall)

Operating Temperature Range: -20°C To +75°C

UL Temperature Rating: 75°C

Bulk Cable Weight: 23.662 Kg/Km

Max. Recommended Pulling Tension: 174.369 N

Min. Bend Radius/Minor Axis: 38.100 mm

### Applicable Specifications and Agency Compliance (Overall)

#### Applicable Standards & Environmental Programs

NEC/(UL) Specification: FPLR

NEC Articles: 760

EU Directive 2011/65/EU (ROHS II): Yes

EU CE Mark: Yes

## METRIC MEASUREMENT VERSION

### 5320UL Multi-Conductor - Commercial Applications - 2 Conductors Cabled

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

#### Flame Test

UL Flame Test:	UL1666 Vertical Shaft
CSA Flame Test:	FT4

#### Suitability

Suitability - Indoor:	Yes
-----------------------	-----

#### Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	6320UL

### Electrical Characteristics (Overall)

#### Nom. Inductance:

Inductance (µH/m)
0.52496

#### Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)
95.149

#### Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)
20.9984

#### Max. Operating Voltage - UL:

Voltage
300 V RMS

#### Max. Recommended Current:

Description	Current
10C Temperature Rise	5 Amps per conductor @ 25°C ambient

### Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
5320UL D15C500	500 FT	7.500 LB	BLUE		2 #18 PP FRPVC
5320UL D151000	1,000 FT	16.000 LB	BLUE	C	2 #18 PP FRPVC
5320UL 001U1000	1,000 FT	16.000 LB	BROWN		2 #18 PP FRPVC
5320UL 002U1000	1,000 FT	16.000 LB	RED		2 #18 PP FRPVC
5320UL 002U500	500 FT	8.500 LB	RED		2 #18 PP FRPVC
5320UL 0021000	1,000 FT	16.000 LB	RED	C	2 #18 PP FRPVC
5320UL 010U1000	1,000 FT	16.000 LB	BLACK		2 #18 PP FRPVC
5320UL 0101000	1,000 FT	16.000 LB	BLACK		2 #18 PP FRPVC

#### Notes:

C = CRATE REEL PUT-UP.

Revision Number: 3    Revision Date: 08-09-2013

© 2015 Belden, Inc.  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.