


Vishay Semiconductors

IR Receiver Module for Light Barrier Systems



MECHANICAL DATA

Pinning:

 $1 = OUT, 2 = GND, 3 = V_S$

FEATURES

- Low supply current
- · Photo detector and preamplifier in one package
- Internal filter for 38 kHz IR signals
- Shielding against EMI
- Supply voltage: 2.5 V to 5.5 V
- · Visible light is suppressed by IR filter
- Insensitive to supply voltage ripple and noise
- Material categorization:

For definitions of compliance please see www.vishay.com/doc?99912





RoHS

HALOGEN FREE

GREEN (5-2008)


DESCRIPTION

The TSSP4038 is a compact IR receiver for sensor applications. It has a high gain for IR signals at 38 kHz. The detection level does not change when ambient light or strong IR signals are applied. It can receive continuous 38 kHz signals or 38 kHz bursts.


This component has not been qualified according to automotive specifications.

PARTS TABLE			
Carrier frequency 38 kHz	z TSSP4038		
Package	Mold		
Pinning	1 = OUT, 2 = GND, 3 = V _S		
Dimensions (mm)	6.0 W x 6.95 H x 5.6 D		
Mounting Leaded			
Application	Presence sensors		

BLOCK DIAGRAM



APPLICATION CIRCUIT



The external components R₁ and C₁ are optional to improve the robustness against electrical overstress (typical values are R₁ = 100 Ω , C₁ = 0.1 μ F).

Vishay Semiconductors

ABSOLUTE MAXIMUM RATINGS							
PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT			
Supply voltage (pin 3)		Vs	-0.3 to +6.0	V			
Supply current (pin 3)		I _S	5	mA			
Output voltage (pin 1)		V _O	-0.3 to 5.5	V			
Voltage at output to supply		V _S - V _O	-0.3 to (V _S + 0.3)	V			
Output current (pin 1)		Io	5	mA			
Junction temperature		Tj	100	°C			
Storage temperature range		T _{stg}	-25 to +85	°C			
Operating temperature range		T _{amb}	-25 to +85	°C			
Power consumption	T _{amb} ≤ 85 °C	P _{tot}	10	mW			

Note

• Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. This is a stress rating only and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of this specification is not implied. Exposure to absolute maximum rating conditions for extended periods may affect the device reliability.

ELECTRICAL AND OPTICAL CHARACTERISTICS (T _{amb} = 25 °C, unless otherwise specified)						
PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT
Supply current (pin 3)	$E_{v} = 0, V_{S} = 5 V$	I _{SD}	0.55	0.7	0.9	mA
	E _v = 40 klx, sunlight	I _{SH}		0.8		mA
Supply voltage		Vs	2.5		5.5	V
Transmission distance	E_{v} = 0, test signal see fig. 1, IR diode TSAL6200, I_{F} = 200 mA	d		25		m
Output voltage low (pin 1)	$I_{OSL} = 0.5 \text{ mA}, E_e = 2 \text{ mW/m}^2,$ test signal see fig. 1	V _{OSL}			100	mV
Minimum irradiance	Pulse width tolerance: t_{pi} - 5/ f_0 < t_{po} < t_{pi} + 6/ f_0 , test signal see fig. 1	E _{e min.}		0.4	0.7	mW/m²
Maximum irradiance	t_{pi} - 5/f ₀ < t_{po} < t_{pi} + 6/f ₀ , test signal see fig. 1	E _{e max.}	50			W/m ²
Directivity	Angle of half transmission distance	Ψ1/2		± 45		deg

TYPICAL CHARACTERISTICS (T_{amb} = 25 °C, unless otherwise specified)




Fig. 1 - Output Active Low




Fig. 2 - Pulse Length and Sensitivity in Dark Ambient

 V_{OL}

Vishay Semiconductors




Fig. 3 - Output Function

t_{off}




Fig. 4 - Output Pulse Diagram




Fig. 5 - Frequency Dependence of Responsivity




Fig. 6 - Sensitivity vs. Ambient Temperature




Fig. 7 - Relative Spectral Sensitivity vs. Wavelength




Fig. 8 - Directivity







Fig. 9 - Sensitivity vs. Supply Voltage

PACKAGE DIMENSIONS in millimeters






www.vishay.com

Vishay Semiconductors

IR Receiver Modules for Remote Control Systems

Vishay offers stock molded IR receivers in four different packages:

- · Loose packed in tubes, mounted on tape for reel or ammopack, or packed bulk in plastic bags.
- Vishay IR receiver with metal holders are packed in plastic trays. Vishay IR receiver with plastic holders are packed in plastic tubes.



FEATURES

• Material categorization: For definitions of compliance please see www.vishay.com/doc?99912






RoHS **GREEN** (5-2008)

AVAILABLE FOR


- TSOP348...
- TSOP344..
- TSOP343..
- TSOP341..
- TSOP44...
- TSOP48...
- TSOP41...
- TSOP324..
- TSOP323..
- TSOP322...
- TSOP321...
- TSOP24...
- TSOP22...
- TSOP21...
- TSOP345..
- TSOP325...
- TSOP43... • TSOP23...
- TSSP4..
- TSMP4..

PACKAGING DIMENSIONS in millimeters



LOOSE PACKED IN TUBE

ORDERING INFORMATION



M = for repeater/learning applications

S = for sensor applications

d = "digit", please consult the list of available devices create a valid part number.

Example: TSOP4838

PACKAGING QUANTITY

- 90 pieces per tube
- 24 tubes per carton

Molded IR Receiver Packaging Options


Vishay Semiconductors


TAPE AND REEL/AMMOPACK


Up to 3 consecutive components may be missing if the gap is followed by at least 6 components. A maximum of 0.5 % of the components per reel quantity may be missing. At least 5 empty positions are present at the start and the end of the tape to enable insertion.

Tensile strength of the tape: > 15 N

Pulling force in the plane of the tape, at right angles to the reel: > 5 N








VERSION	DIMENSION "H"
BS	20 ± 0.5
PS	23.3 ± 0.5
os	26 ± 0.5

ORDERING INFORMATION



Note

• d = "digit", please consult the list of available devices create a valid part number.

Example: TSOP4838SS1BS12
TSOP2238SS1BS12Z

PACKAGING QUANTITY

- 1000 pieces per reel
- 1000 pieces per ammopack




Molded IR Receiver Packaging Options

Vishay Semiconductors

BULK PACKAGING

The option "BK" signifies bulk packaging in conductive plastic bags. A maximum of 0.3 % of the components per box may be missina.

ORDERING INFORMATION



S = for sensor applications

Note

• d = "digit", please consult the list of available devices create a valid part number.


EXAMPLE: TSOP4838SS1BK

TSOP2238SS1BK

PACKAGING QUANTITY

- 250 pieces per bag (each bag is individually boxed)
- 6 bags per carton

OUTER PACKAGING





Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.

Revision: 02-Oct-12 Document Number: 91000