www.vishay.com

Vishay General Semiconductor

# Surface Mount Trench MOS Barrier Schottky Rectifier



PRIMARY CHARACTERISTICS				
I <sub>F(AV)</sub>	8.0 A			
V <sub>RRM</sub>	45 V			
I <sub>FSM</sub>	120 A			
$V_F$ at $I_F$ = 8.0 A ( $T_A$ = 125 °C)	0.40 V			
T <sub>J</sub> max.	150 °C			
Package	DO-221BC (SMPA)			
Diode variation	Single die			

## FEATURES

- Very low profile typical height of 0.95 mm
- Ideal for automated placement
- Trench MOS Schottky technology
- Low power losses, high efficiency
- Low forward voltage drop
- AEC-Q101 qualified
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 °C
- Material categorization: For definitions of compliance please see <u>www.vishay.com/doc?99912</u>

### TYPICAL APPLICATIONS

For use in low voltage, high frequency inverters, freewheeling, DC/DC converters, and polarity protection applications.

### **MECHANICAL DATA**

Case: DO-221BC (SMPA)

Molding compound meets UL 94 V-0 flammability rating Base P/N-M3 - halogen-free, RoHS-compliant, and commercial grade

Base P/NHM3 - halogen-free, RoHS-compliant, and AEC-Q101 qualified

**Terminals:** Matte tin plated leads, solderable per J-STD-002 and JESD22-B102

M3 suffix meets JESD 201 class 2 whisker test, HM3 suffix meets JESD 201 class 2 whisker test

Polarity: Color band denotes cathode end

<b>MAXIMUM RATINGS</b> ( $T_A = 25 \text{ °C}$ unless otherwise noted)				
PARAMETER	SYMBOL	V8PAL45	UNIT	
Device marking code		8L45		
Maximum repetitive peak reverse voltage	V <sub>RRM</sub>	45	V	
Maximum DC forward current	I <sub>F</sub> <sup>(1)</sup>	8.0	Α	
	I <sub>F</sub> <sup>(2)</sup>	4.0		
Peak forward surge current 10 ms single half sine-wave superimposed on rated load	I <sub>FSM</sub>	120	А	
Operating junction and storage temperature range	T <sub>J</sub> , T <sub>STG</sub>	- 40 to + 150	°C	

Notes

<sup>(1)</sup> Units mounted on 3 cm x 3 cm Aluminum, 2 oz. PCB

<sup>(2)</sup> Free air, mounted on recommended copper pad area

1



COMPLIANT

HALOGEN

FREE

www.vishay.com

# Vishay General Semiconductor

<b>ELECTRICAL CHARACTERISTICS</b> ( $T_A = 25 \text{ °C}$ unless otherwise noted)						
PARAMETER	TEST CO	TEST CONDITIONS		TYP.	MAX.	UNIT
Instantaneous forward voltage	I <sub>F</sub> = 4.0A	T <sub>A</sub> = 25 °C	V <sub>F</sub> <sup>(1)</sup>	0.43	-	v
	$I_{F} = 8.0 \text{ A}$			0.49	0.57	
	I <sub>F</sub> = 4.0 A	T <sub>A</sub> = 125 °C		0.32	-	
	I <sub>F</sub> = 8.0 A			0.40	0.48	
Reverse current	V <sub>B</sub> = 45 V	T <sub>A</sub> = 25 °C T <sub>A</sub> = 125 °C	I <sub>R</sub> (2)	-	1850	μA
	v <sub>R</sub> = 43 v	T <sub>A</sub> = 125 °C		11	30	mA
Typical junction capacitance	4.0 V, 1 M⊦	4.0 V, 1 MHz		1400	-	pF

#### Notes

<sup>(1)</sup> Pulse test: 300 µs pulse width, 1 % duty cycle

<sup>(2)</sup> Pulse test: Pulse width  $\leq$  5 ms

<b>THERMAL CHARACTERISTICS</b> ( $T_A = 25$ °C unless otherwise specified)				
PARAMETER	SYMBOL	V8PAL45	UNIT	
Typical thermal resistance	R <sub>0JA</sub> <sup>(1)</sup>	100	°C/W	
	R <sub>0JM</sub> <sup>(2)</sup>	5		

#### Notes

<sup>(1)</sup> Free air, mounted on recommended PCB, 2 oz. pad area; thermal resistance  $R_{0JA}$  - junction to ambient

 $^{(2)}$  Units mounted on 3 cm x 3 cm Aluminum, 2 oz. pad area; thermal resistance  $R_{0JM}$  - junction to mount

ORDERING INFORMATION (Example)					
PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE	
V8PAL45-M3/I	0.032	I	14 000	13" diameter plastic tape and reel	
V8PAL45HM3/I <sup>(1)</sup>	0.032	Ι	14 000	13" diameter plastic tape and reel	

#### Note

<sup>(1)</sup> AEC-Q101 qualified

### **RATINGS AND CHARACTERISTICS CURVES**

(T<sub>A</sub> = 25 °C unless otherwise noted)




Fig. 1 - Maximum Forward Current Derating Curve




Fig. 2 - Forward Power Loss Characteristics


Revision: 30-Jul-13

2

Document Number: 87908

For technical questions within your region: <u>DiodesAmericas@vishay.com</u>, <u>DiodesAsia@vishay.com</u>, <u>DiodesEurope@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>








Fig. 3 - Typical Instantaneous Forward Characteristics





Fig. 4 - Typcial Reverse Leakage Characteristics






Fig. 6 - Typcial Transient Thermal Impedance





Fig. 7 - Thermal Resistance Junction to Ambient vs. Copper Pad Areas

Revision: 30-Jul-13

3

Document Number: 87908


For technical questions within your region: <u>DiodesAmericas@vishay.com</u>, <u>DiodesAsia@vishay.com</u>, <u>DiodesEurope@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>



WISHAY. www.vishay.com

# PACKAGE OUTLINE DIMENSIONS in inches (millimeters)

DO-221BC (SMPA)





Vishay

# Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

# **Material Category Policy**

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.