

# 1.4kW Single-Phase Metered PDU, 120V Outlets (13 5-15R), 5-15P, 100-127V Input, 15ft Cord, 1U Rack-Mount

MODEL NUMBER: PDUMH15



## Description

Tripp Lite Metered PDU / Power Distribution Units offer real-time local reporting of load level in amps via built-in digital meter. Enables visual current monitoring of PDU output current to prevent circuit overloads as additional equipment is added. Offers reliable rackmount multi-outlet power distribution from any protected UPS, generator or mains input power source. High quality design includes rugged all-metal housing and secure rackmount installation with included mounting accessories.

## Features

- 15A single phase 120V Metered Power Distribution Unit / PDU (Agency de-rated to 12A continuous)
- Built-in 2 digit visual meter continuously reports PDU load level in amps
- Attached NEMA 5-15P 15A 120V input plug with 15 ft. / 4.5m line cord
- 1U horizontal rackmount format installs in one rack space
- 13 NEMA 5-15R outlets (1 front facing / 12 rear)
- Mounting flanges support installation in 2 and 4 post racks, with additional support for wall-mount and under-counter installation formats
- Optional PDUSIDEBRKT enables 0U vertical rackmount in compatible racks
- Back panel grounding lug

## Specifications

OVERVIEW	
Style	Rackmount, Vertical Rackmount, Wallmount/Under-Counter
PDU Type	Metered

## Highlights

- Metered single phase 15A 120V PDU
- 1U horizontal rackmount, Digital current meter
- NEMA 5-15P input with 15 ft. / 4.5m line cord
- 13 NEMA 5-15R outlets (1 front / 12 rear)
- Reversible housing, 4.5 in. / 11.4 cm depth

## Applications

- Multi-outlet power distribution unit with digital current monitoring is the ideal means of powering multiple loads in 19 inch rackmount, wall-mount, and under-counter applications such as internetworking, PC systems, telecommunications, audio visual, security, sound reinforcement, and more. Ideal distribution of alternate and sinewave UPS and generator power or commercially derived AC power to connected equipment.

## Package Includes

- PDUMH15 Metered rackmount PDU
- Owner's manual with warranty information



<b>OUTPUT</b>	
Output Capacity Details	1.44kW (120V), 1.52kW (127V), 1.2kW (100V); 15A maximum (Agency de-rated to 12A continuous)
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(13) 5-15R
Output Nominal Voltage	100-127V nominal, single phase
Overload Protection	15A Breaker
Outlet Type	NEMA 5-15R
<b>INPUT</b>	
PDU Input Voltage	100; 120; 127
Recommended Electrical Service	15A 120V
Maximum Input Amps	15
Maximum Input Amps Details	Agency de-rated to 12A continuous
PDU Plug Type	NEMA 5-15P
Input Cord Length (ft.)	15
Input Cord Length (m)	4.57
Input Phase	Single-Phase
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Front Panel LCD Display	Digital display reports total PDU output current in amps
Switches	n/a
<b>PHYSICAL</b>	
Shipping Dimensions (hwd / in.)	2.25 x 20.5 x 10
Shipping Dimensions (hwd / cm)	5.72 x 52.07 x 25.4
Shipping Weight (lbs.)	5.2
Shipping Weight (kg)	2.36
Unit Dimensions (hwd / in.)	1.75 x 17.5 x 4.5
Unit Dimensions (hwd / cm)	4.45 x 44.45 x 11.43
Unit Weight (lbs.)	4.5
Unit Weight (kg)	2.04
Material of Construction	Metal
Form Factors Supported	1U rackmount, 0U vertical rackmount, wall-mount, and under-counter installation
PDU Form Factor	Horizontal (1U, 2U, etc)
Outlets Measurement (Center to Center)	Rear Side = 30.20mm



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

<b>ENVIRONMENTAL</b>	
Storage Temperature Range	5 to 122F (-15 to 50C)
Relative Humidity	5-95% non-condensing
Operating Elevation (ft.)	0-10,000
Operating Elevation (m)	0-3000
<b>SPECIAL FEATURES</b>	
TVSS Grounding	Rear grounding lug
<b>CERTIFICATIONS</b>	
Certifications	Tested to UL60950-1 (USA) and CAN/CSA C22.2 No. 60950-1-03 (Canada), RoHS Compliant
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.