

LTA-Series

Single Pole Lighted Rocker Switches

The illuminated predecessor to the Corvette series whose versatility has allowed it to stand the test of time. Traditional styling coupled with self cleaning contacts, integrated wire leads, and various actuator choices has made the LTA-Series appeal to a wide range of markets including Appliance, HVAC, Food service, Transportation, and sundry other markets as well.



Carling Technologies®

Innovative Designs. Powerful Solutions.

INNOVATIVE DESIGNS. POWERFUL SOLUTIONS.

Carling Technologies, Inc.
60 Johnson Avenue • Plainville, CT 06062-1177
Phone: (860) 793-9281 • Fax: (860) 793-9231
Email: sales@carlingtech.com • www.carlingtech.com

Dielectric Strength

UL/CSA:
1000V - live to dead metal parts
750V - across open contacts

Electrical Life

100,000 cycles

Mechanical Life

100,000 cycles

Operating Temperature

32°F to 185°F (0°C to 85°C)

LTA201 - P R - B -A 125N

¹
Base Part Number

²
Actuator
Style

³
Actuator
Color

⁴
Bezel
Color/Style

⁵
Lens
Color

⁶
Lamp Voltage

1 BASE PART NUMBER: SERIES/CIRCUITRY/RATING¹/TERMINATION

10A 250VAC; 15A 125VAC; 3/4 HP 125-250VAC
Solder Lugs .250 Tabs .187 Tabs Wire Leads
OFF-NONE-ON LTA200 LTA201 LTA203 LTA205

2 ACTUATOR STYLE³

T Rocker PS Short Paddle
P Paddle

2 ACTUATOR STYLE¹

A Amber R Red
C Clear G Green²

4 BEZEL COLOR¹

B Black W White

5 LENS COLOR^{2,3}


/ No Lens -G Green
-A Amber -R Red
-C Clear -LU Blue

6 LAMP VOLTAGE²




006V 6V incandescent 024V 24V incandescent
012V 12V incandescent 125N 125V neon
018V 18V incandescent 250N 250V neon

Notes:

- Additional ratings and colors are available. Consult factory for details.
- Neon lamps not recommended with green or blue rocker/lenses.
- Lens color is specified only if actuator style is P or PS. If style is T (rocker), then use / as the code in position 5.



.250 TAB (Q.C.)	SOLDER LUG	.187 TAB (Q.C.)	INTEGRATED WIRE LEAD (no exposed conductors)
TERMINAL TYPE			



MOUNTING HOLE
Panel Thickness:
.020[.508] min. to
.250[6.35] max.