



TL Mini Standard Colours

TL Mini 8W/33-640 1FM

Low-pressure mercury discharge lamps with a tubular 16 mm envelope

Product data

• General Characteristics

System Description	na [-]
Cap-Base	G5
Bulb	T5 [16 mm]
Life to 10% failures EM	5000 hr
Life to 10% fail Preheat EL,3h	5000 hr
Life to 10% fail Nonpreh EL,3h	3000 hr
Life to 50% failures EM	10000 hr
Life to 50% fail Preheat EL,3h	10000 hr
Life to 50% fail Nonpreh EL,3h	7000 hr

• Light Technical Characteristics

Colour Code	33-640
Colour Rendering Index	60 Ra8
Colour Designation	Cool White
Colour Temperature	4100 K
Lamp Luminous Flux EM	410 Lm
Lamp Luminous Efficacy EM	51 Lm/W
Lumen Maintenance 2000h	80 %
Lumen Maintenance 5000h	70 %
Lumen Maintenance 10000h	58 %
Average Luminance EM	0.90 cd/cm ²

Chromaticity Coordinate X	377 -
Chromaticity Coordinate Y	381 -

• Electrical Characteristics

Lamp Wattage	8 W
Lamp Wattage EM	7.1 W
Lamp Voltage	56 V
Lamp Current EM	0.150 A
Dimmable	yes

• Environmental Characteristics

Energy Efficiency Label (EEL)	A
Mercury (Hg) Content	4.4 mg
Energy consumption kWh/1000h	8 kWh

• Product Dimensions

Base Face to Base Face A	288.3 (max) mm
Insertion Length B	293.0 (min), 295.4 (max) mm
Overall Length C	302.5 (max) mm
Diameter D	16 (max) mm

• Product Data

Order code	704733 27
Full product code	871150070473327
Full product name	TL Mini 8W/33-640 1FM
Order product name	TL Mini 8W/33-640 1FM/10X25CC
Pieces per pack	1


PHILIPS

TL Mini Standard Colours

Packing configuration 10X25CC
 Packs per outerbox 250
 Bar code on pack - EAN1 8711500704733
 Bar code on intermediate packing - EAN2 8711500718433


Bar code on outerbox - EAN3 8711500718440
 Logistic code(s) - 12NC 928001003318
 ILCOS code FD-8/41/2B-E-G5
 Net weight per piece 27.000 gr

Dimensional drawing





TL Mini 8W/33-640 1FM

Product	A (Max)	B (Min)	B (Max)	C (Max)	D (Max)
TL Mini 8W/33-640	288.3	293.0	295.4	302.5	16



G5

Photometric data



© 2014 Koninklijke Philips N.V. (Royal Philips)
 All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

www.philips.com/lighting

2014, December 20
 data subject to change