



Miniature Quick Wire Sockets



'Just push-in wire & tighten screw'

About Labfacility

Formed in 1971, Labfacility specialize in the field of Temperature and Process Measurement.

We are the largest UK manufacturer of both temperature sensors and thermocouple connectors


Quality & Service

Quality and Service are key elements in the continued growth of Labfacility.

Technical support is always freely available from our experienced technical sales teams and the company has ISO9001 accreditation.

- Miniature quick wire socket allowing rapid termination of wires
- Easy 'jab-in' connection, just push-in wire & tighten screw
- Available in Thermocouple types K, J, T, E, N, R/S, B & Copper
- For Types K, J, T, E & N contacts are made from true Thermocouple alloys
- Contacts are polarised to prevent incorrect connection
- Colour coded in accordance with IEC specification
- Maximum continuous temperature 220 deg°C

T/C Type	Colour Code (IEC)	+Positive Contact (alloy type)	-Negative Contact (alloy type)	Part Code	Farnell Order Code
K	Green	+Nickel Chromium	-Nickel Alloy	IM-K-FQ	381-0446
J	Black	+Iron	-Copper Nickel	IM-J-FQ	381-0434
T	Brown	+Copper	-Copper Nickel	IM-T-FQ	381-0460
N	Pink	+Nickel/Chro/Silicon	-Nickel Silicon	IM-N-FQ	234-7031
Copper	White	+Copper	-Copper	IM-CU-FQ	381-0471
B	Grey	+Copper	-Copper	IM-B-FQ	234-7029
E	Violet	+Nickel Chromium	-Copper Nickel	IM-E-FQ	234-7030
R/S	Orange	+Copper	-Copper Alloy	IM-R/S-FQ	234-7032



FAR012/0313. Miniature Quick Wire Sockets

Contact Details

Email
sales@labfacility.com

Website
www.labfacility.com