

LABFACILITY

TEMPERATURE & PROCESS TECHNOLOGY


JIS Miniature Thermocouple Socket with Stainless Steel mounting bracket




'Contacts are polarized to ensure correct connection'

- Miniature size in-line Thermocouple Socket with stainless steel panel mounting bracket
- Contacts are polarized to ensure correct connection
- Available in Thermocouple types K, J
- For Types K, J contacts are made from true Thermocouple alloys
- Colour coded in accordance with JIS specification
- Maximum continuous operating temperature 220 deg°C

T/C Type	Colour Code (JIS)	+Positive (alloy type)	-Negative (alloy type)	Labfacility Code	Farnell Code
K	Blue	+Nickel Chromium	-Nickel Alloy	JM-K-SSPF	234-7185
J	Yellow	+Iron	-Copper Nickel	JM-J-SSPF	234-7184



Recommended aperture size and hole pitch for panel mounting



Drill and counter sink to suit M2.5*10 typical

About Labfacility

Formed in 1971, Labfacility specialize in the field of Temperature and Process Measurement.

We are the largest UK manufacturer of both temperature sensors and thermocouple connectors

Quality & Service

Quality and Service are key elements in the continued growth of Labfacility.

Technical support is always freely available from our experienced technical sales teams and the company has ISO9001 accreditation.

Contact Details

Email
sales@labfacility.com

Website
www.labfacility.com