

LABFACILITY

TEMPERATURE & PROCESS TECHNOLOGY

JIS Standard In-Line Thermocouple Sockets

About Labfacility

Formed in 1971, Labfacility specialize in the field of Temperature and Process Measurement.

We are the largest UK manufacturer of both temperature sensors and thermocouple connectors

Quality & Service

Quality and Service are key elements in the continued growth of Labfacility.


Technical support is always freely available from our experienced technical sales teams and the company has ISO9001 accreditation.



'Accepts standard round plug pins'

- Standard in-line thermocouple socket with connections to suit thermocouple type being used
- Accepts standard round plug pins
- Suitable for industrial applications
- Available in Thermocouple types K, J
- For Types K, J contacts are made from true Thermocouple alloys
- Contacts are polarised to prevent incorrect connection
- Colour coded in accordance with JIS specification
- Maximum continuous operating temperature 220 deg°C

T/C Type	Colour Code (JIS)	+Positive (alloy type)	-Negative (alloy type)	Labfacility Code	Farnell Code
K	Blue	+Nickel Chromium	-Nickel Alloy	JS-K-F	234-7194
J	Yellow	+Iron	-Copper Nickel	JS-J-F	234-7193



FAR057/0613 JIS Standard In-Line Thermocouple Sockets

Contact Details

Email
sales@labfacility.com

Website
www.labfacility.com