



Glass fibre Insulated Flat Pair Types 'K', 'J' & 'T' 1/0.3 solid strand– to IEC584



- Glass fibre insulated extension cable in thermocouple types; KX, JX or TX
- Glass fibre insulated flat pair construction, conductors laid flat, Glass fibre insulated with Glass fibre overall, silicone varnished throughout
- Good temperature resistance but not suitable where fluids are present
- Available in solid 1/0.3mm conductors
- Available in 10 or 50 metre reel lengths
- All types; conductors are made from associated K, J or T thermocouple alloy type
- Tolerance Class 2 to IEC-584
- Insulation rating -60°C to 350°C (short periods up to 400°C)
- Colour code (cores & jacket) to IEC-584-3

T/C Type	Conductors	mm ²	Cores	Jacket	Reel Length	order code
KX	1/0.3mm	0.072	+Green/-White	Green	10 metres	708-5930
KX	1/0.3mm	0.072	+Green/-White	Green	50 metres	708-5941
JX	1/0.3mm	0.072	+Black/-White	Black	10 metres	708-5928
TX	1/0.3mm	0.072	+Brown/-White	Brown	10 metres	708-5953

About Labfacility

Formed in 1971, Labfacility specialize in the field of Temperature and Process Measurement.

We are the largest UK manufacturer of both temperature sensors and thermocouple connectors

Quality & Service

Quality and Service are key elements in the continued growth of Labfacility.

Technical support is always freely available from our experienced technical sales teams and the company has ISO9001 accreditation.

Contact Details

Email
sales@labfacility.com

Website
www.labfacility.com

