

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

22-01-2097

Status:

Active

Overview:

KK® Interconnect System - Molex

Description:

KK® 254 Crimp Housing, Friction Ramp, 9 Circuits



image - Reference onlySeries

Documents:

3D Model

Drawing (PDF)

Product Specification PS-10-07 (PDF)

Packaging Specification PK-2695-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	Crimp Housings
Series	2695
Application	Signal, Wire-to-Board
Overview	KK® Interconnect System - Molex
Product Name	KK® 254
UPC	800753689978
Physical	
Circuits (maximum)	9
Color - Resin	Natural (White)
Flammability	94V-0
Gender	Female
Glow-Wire Compliant	No
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	0.954/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Stackable	No
Temperature Range - Operating	See Product Specification
Material Info	
Old Part Number	2695-09R
Reference - Drawing Numbers	
Packaging Specification	PK-2695-001
Product Specification	PS-10-07
Sales Drawing	SD-2695

EU RoHS

ELV and RoHS Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Low-Halogen

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

2695Series

Mates With

KK®254 PCB Headers [42375](#) , [42377](#) , [42376](#) , [4030](#) , [6373](#) , [6410](#)

Use With

[2759](#) , [4809](#) KK® Crimp terminal

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION