


## 7876A Composite - Composite Data, Audio, Video, Security and Control Cable



For more Information  
please call

1-800-Belden1



### General Description:

Composite - (2) Cat 5e 4-bonded-pair 24 AWG unshielded plus (2) Series 6 Coax with Duobond Plus® Bonded Tri-shield, polyolefin insulation on the pairs; Gas-injected FPE insulation on the coax, F-R PVC jackets, overall F-R PVC jacket.

### Usage (Overall)

Suitable Applications: HDTV

### Coax

#### Physical Characteristics

##### Conductor

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (in.)
2	18	Solid	BC - Bare Copper	0.040

##### Insulation

Insulation Material:

Insulation Material	Dia. (in.)
Gas-injected FPE - Foam Polyethylene	0.180

##### Inner Shield

Inner Shield Material:

Layer #	Inner Shield Trade Name	Type	Inner Shield Material	% Coverage (%)
1	Bonded Duofoil®	Tape	Bonded Aluminum Foil-Polyester Tape-Aluminum Foil	100.000
2		Braid	AL - Aluminum	80.000
3		Tape	Bonded Aluminum Foil-Polyester Tape w/Shorting Fold	100.000

##### Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Outer Jacket Diameter:

Nom. Dia. (in.)
0.275

Outer Jacket Color Code Chart:

Number	Color
1	Black
2	White

### Applicable Specifications and Agency Compliance Applicable Standards & Environmental Programs

Series Type: Series 6

### Electrical Characteristics

Nom. Characteristic Impedance:

Impedance (Ohm)
75

Nom. Inductance:

Inductance (µH/ft)
0.097

Nom. Capacitance Conductor to Shield:

Capacitance (pF/ft)
16.200

Nominal Velocity of Propagation:

VP (%)
83.000

Nominal Delay:

## 7876A Composite - Composite Data, Audio, Video, Security and Control Cable

Delay (ns/ft)
1.200

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
6.400

Nom. Inner Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
4.600

Minimum Structural Return Loss:

Start Freq. (MHz)	Stop Freq. (MHz)	Min. SRL (dB)
5.000	1000.000	20.000
1000.000	2250.000	15.000
2250.000	3000.000	10.000

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100 ft.)
5.000	0.500
55.000	1.400
211.000	2.600
500.000	4.100
750.000	5.100
862.000	5.500
1000.000	6.000
1450.000	7.800
1800.000	8.600
2250.000	9.800
3000.000	11.300

Max. Attenuation:

Freq. (MHz)	Attenuation (dB/100 ft.)
5.000	0.670
55.000	1.600
211.000	2.870
500.000	4.480
750.000	5.590
862.000	5.980
1000.000	6.540
1450.000	8.000
1800.000	8.800
2250.000	10.000
3000.000	11.900

Max. Operating Voltage - UL:

350 V RMS

Shield Effectiveness:

Start Frequency (MHz)	Stop Frequency (MHz)	Shield Effectiveness (dB)
5.000	50.000	105.000
50.000	1000.000	125.000

### Twisted Pair

#### Physical Characteristics

##### Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material	Dia. (in.)
8	24	Solid	BC - Bare Copper	0.020

##### Insulation

Insulation Material:

Insulation Material	Dia. (in.)
PO - Polyolefin	0.038

Twisted Pair Color Code Chart:

Number	Color
1	White/Blue Stripe and Blue
2	White/Orange Stripe and Orange
3	White/Green Stripe and Green
4	White/Brown Stripe and Brown

##### Individual Shield

##### Outer Jacket

Outer Jacket Material:

## 7876A Composite - Composite Data, Audio, Video, Security and Control Cable

**Outer Jacket Material**  
PVC - Polyvinyl Chloride

Outer Jacket Ripcord: Yes

Outer Jacket Color Code Chart:

Number	Color
1	Blue
2	Green

### Overall Diameter

Overall Nominal Diameter: 0.200 in.

### Electrical Characteristics

Nom. Mutual Capacitance:

**Capacitance (pF/ft)**  
15.000

Nominal Velocity of Propagation:

**VP (%)**  
70.000

Maximum Conductor DC Resistance:

**DCR @ 20°C (Ohm/100 m)**  
9.380

Max. Operating Voltage - UL:

**Voltage**  
300 V RMS

Other Electrical Characteristic 1: Third party verified to TIA/EIA-568-B.2, Category 5e/

Premise Cable Electrical Table 1:

Freq. (MHz)	Max. Attenuation (dB/100 m)	Min. PSNEXT (dB)	Min. PSACR (dB)	Min RL (dB)
1.0	2.000	62.3	60	20.000
4.0	4.100	53.3	49	23.000
8.0	5.800	48.8	43	24.500
10.0	6.500	47.3	41	25.000
16.0	8.200	44.3	36	25.000
20.0	9.300	42.8	34	25.000
25.0	10.400	41.3	31	24.300
31.25	11.700	39.9	28	23.600
62.5	17.000	35.4	19	21.500
100	22.000	32.3	11	20.100

Premise Cable Electrical Table 2:

Freq. (MHz)	Input (Unfitted) Imp. (Ohms)	Min. PSELFEXT (dB)
1.0	100 ± 15%	60.8
4.0	100 ± 15%	48.7
8.0	100 ± 15%	42.7
10.0	100 ± 15%	40.8
16.0	100 ± 15%	36.7
20.0	100 ± 15%	34.7
25.0	100 ± 15%	32.8
31.25	100 ± 15%	30.9
62.5	100 ± 15%	24.8
100	100 ± 15%	20.8

### Physical Characteristics (Overall)

#### Outer Shield

Outer Shield Material:

**Outer Shield Material**  
Unshielded

#### Outer Jacket

Outer Jacket Material:

**Outer Jacket Material**  
PVC - Polyvinyl Chloride

Outer Jacket Ripcord: Yes

### Overall Cable

Overall Nominal Diameter: 0.610 in.

### Mechanical Characteristics (Overall)

## 7876A Composite - Composite Data, Audio, Video, Security and Control Cable

Operating Temperature Range:	-20°C to +75°C
Bulk Cable Weight:	134 lbs/1000 ft.
Max. Recommended Pulling Tension:	262 lbs.
Min. Bend Radius/Minor Axis:	6.250 in.

### Applicable Specifications and Agency Compliance (Overall)

#### Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMR
CEC/(UL) Specification:	CMG
EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Other Specification:	NEMA WC-63.1, Category 5e

#### Flame Test

UL Flame Test:	UL1666 Riser
CSA Flame Test:	FT4

#### Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

### Notes (Overall)

**Notes:** Overall jacket sequentially marked. Shielding effectiveness determined from screening attenuation measurement when tested in accordance with IEC 61196-1.

### Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
--------	-------	-------------	-------	-------	-----------

Revision Number: 0    Revision Date: 09-26-2012

© 2015 Belden, Inc.  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.