

9451P Multi-Conductor - Single-Pair Cable



For more Information
please call

1-800-Belden1

**General Description:**

22 AWG stranded (7x30) TC conductors, twisted pair, FEP insulation, overall Beldfoil shield (100% coverage), 22 AWG stranded TC drain wire, Flamarrest® jacket.

Physical Characteristics (Overall)**Conductor**

AWG:

# Pairs	AWG	Stranding	Conductor Material
1	22	7x30	TC - Tinned Copper

Total Number of Conductors:

2

Insulation

Insulation Material:

Insulation Material	Wall Thickness (in.)
FEP - Fluorinated Ethylene Propylene	.007

Outer Shield

Outer Shield Material:

Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
22	7x30	TC - Tinned Copper

Outer Jacket

Outer Jacket Material:

Outer Jacket Trade Name	Outer Jacket Material
Flamarrest®	LS PVC - Low Smoke Polyvinyl Chloride

Overall Cable

Overall Nominal Diameter:

0.127 in.

Pair

Pair Color Code Chart:

Number	Color
1	Black & Red

Mechanical Characteristics (Overall)

Operating Temperature Range:	-20°C To +75°C
UL Temperature Rating:	60°C
Bulk Cable Weight:	14 lbs/1000 ft.
Max. Recommended Pulling Tension:	27 lbs.
Min. Bend Radius/Minor Axis:	1.250 in.

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

NEC/(UL) Specification:	CMP
CEC/C(UL) Specification:	CMP
EU Directive 2011/65/EU (RoHS II):	Yes
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes

9451P Multi-Conductor - Single-Pair Cable

EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MIL Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:	NFPA 262
CSA Flame Test:	FT6

Plenum/Non-Plenum

Plenum (Y/N):	Yes
Non-Plenum Number:	9451

Electrical Characteristics (Overall)

Nom. Inductance:

Inductance (µH/ft)
.15

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)
35

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/ft)
67

Nominal Velocity of Propagation:

VP (%)
69

Nominal Delay:

Delay (ns/ft)
1.47

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
14.1

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
14.3

Max. Operating Voltage - UL:

Voltage
300 V RMS

Max. Recommended Current:

Current
2.9 Amps per conductor @ 25°C

Notes (Overall)

Notes: The jacket and shield are bonded so both can be removed on automatic stripping equipment. Drain wire is inside foil shield.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
9451P N3UU1000	1,000 FT	16.000 LB	GREEN, MIL		FSPR #22 FEP PLENUM PVC
9451P N3U5000	5,000 FT	75.000 LB	GREEN, MIL	C	FSPR #22 FEP PLENUM PVC
9451P 001U1000	1,000 FT	16.000 LB	BROWN		FSPR #22 FEP PLENUM PVC
9451P 0015000	5,000 FT	75.000 LB	BROWN	C	FSPR #22 FEP PLENUM PVC
9451P 002U1000	1,000 FT	16.000 LB	RED		FSPR #22 FEP PLENUM PVC
9451P 0025000	5,000 FT	75.000 LB	RED	C	FSPR #22 FEP PLENUM PVC
9451P 003U1000	1,000 FT	16.000 LB	ORANGE		FSPR #22 FEP PLENUM PVC
9451P 0035000	5,000 FT	75.000 LB	ORANGE	C	FSPR #22 FEP PLENUM PVC
9451P 004U1000	1,000 FT	16.000 LB	YELLOW		FSPR #22 FEP PLENUM PVC
9451P 0045000	5,000 FT	75.000 LB	YELLOW	C	FSPR #22 FEP PLENUM PVC
9451P 006U1000	1,000 FT	16.000 LB	BLUE, LIGHT		FSPR #22 FEP PLENUM PVC
9451P 0065000	5,000 FT	75.000 LB	YELLOW	C	FSPR #22 FEP PLENUM PVC
9451P 007U1000	1,000 FT	16.000 LB	VIOLET		FSPR #22 FEP PLENUM PVC
9451P 0075000	5,000 FT	75.000 LB	VIOLET	C	FSPR #22 FEP PLENUM PVC
9451P 008U1000	1,000 FT	16.000 LB	GRAY		FSPR #22 FEP PLENUM PVC
9451P 0085000	5,000 FT	75.000 LB	GRAY	C	FSPR #22 FEP PLENUM PVC
9451P 009U1000	1,000 FT	16.000 LB	WHITE		FSPR #22 FEP PLENUM PVC

9451P Multi-Conductor - Single-Pair Cable

9451P 0095000	5,000 FT	75.000 LB	WHITE	C	FSPR #22 FEP PLENUM PVC
9451P 010U1000	1,000 FT	16.000 LB	BLACK		FSPR #22 FEP PLENUM PVC
9451P 010I1000	1,000 FT	15.000 LB	BLACK		FSPR #22 FEP PLENUM PVC
9451P 0105000	5,000 FT	75.000 LB	BLACK	C	FSPR #22 FEP PLENUM PVC

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 1 Revision Date: 07-29-2013

© 2015 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.