

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [45750-1111](#)  
**Status:** **Active**  
**Overview:** [Mini-Fit® Plus Connector System](#)  
**Description:** Mini-Fit® Plus Crimp Terminal, 18-20 AWG, Reel, Copper (Cu) Alloy, Tin (Sn)

**Documents:**

[Drawing \(PDF\)](#) [Packaging Specification PK-45750-001 \(PDF\)](#)  
[Product Specification PS-45750-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Crimp Terminals
Series	<a href="#">45750</a>
Application	Power
Comments	Current = 13A max. per circuit when header is mated to a receptacle loaded with <a href="#">45750</a> series terminals crimped to 16 AWG wire. . See Molex product specification PS-45750-001 for additional current derating information.
Crimp Quality Equipment Overview	Yes
Packaging Alternative	<a href="#">Mini-Fit® Plus Connector System</a>
Product Name	<a href="#">45750-1112</a> (Loose)
UPC	Mini-Fit® Plus 822350286015

**Physical**

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Copper-Nickel-Silicon
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.150/g
Packaging Type	Reel
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.80-3.10mm
Wire Size AWG	18, 20
Wire Size mm <sup>2</sup>	N/A


**Electrical**

Current - Maximum per Contact	13.0A
Voltage - Maximum	600V

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification	PK-45750-001
Product Specification	PS-45750-001
Sales Drawing	SD-45750-001, SD-46018-001, SDIN-45750-001



*image - Reference only*

**EU RoHS**

**ELV and RoHS Compliant**  
**REACH SVHC Contains SVHC: No Low-Halogen Status Low-Halogen**

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

[45750Series](#)

**Mates With**

[46012](#) Mini-Fit® Plus Crimp Terminal

**Use With**

[5557](#) Mini-Fit Jr.™, [30067](#) Mini-Fit® TPA, [42474](#) Mini-Fit® BMI Panel Mount, [43760](#) Mini-Fit® BMI, [44516](#) Mini-Fit® BMI Panel Mount Slide-N-Lock

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

<b>Description</b>	<b>Product #</b>
Extraction Tool	<a href="#">0011030044</a>
Hand Crimp Tool for Male and Female Crimp Terminals, 16-24 AWG Wire	<a href="#">0638190900</a>

FineAdjust™ Applicator for Insulation OD 2.50-2.95mm, 18-24 AWG Wire	<u>0639002600</u>
FineAdjust™ Applicator for Insulation OD 1.65-2.05mm, 18-24 AWG Wire	<u>0639002900</u>
FineAdjust™ Applicator for Insulation OD 1.90-2.30mm - 18-24 AWG	<u>0639015600</u>
FineAdjust™ Applicator for Insulation OD 1.40-1.70mm - 18-24 AWG	<u>0639023900</u>
FineAdjust™ Applicator for Insulation OD 2.50-2.95mm Optimized for 18 AWG Only	<u>0639024800</u>
FineAdjust™ Applicator for Insulation OD 2.30-2.60mm - 18-24 AWG	<u>0639024900</u>
T2 Terminator™ for insulation OD 2.50-2.95mm - 18-24 AWG	<u>0639102600</u>
T2 Terminator™ for insulation OD 1.65 – 2.05mm – 18 – 24 AWG	<u>0639102900</u>
T2 Terminator™ for insulation OD 1.90-2.30mm - 18-24 AWG	<u>0639115600</u>
T2 Terminator™ for insulation OD 1.40-1.70mm - 18-24 AWG	<u>0639123900</u>
T2 Terminator™ for insulation OD 2.50-2.95mm optimized for 18 AWG only	<u>0639124800</u>
T2 Terminator™ for insulation OD 2.30-2.60mm - 18-24 AWG	<u>0639124900</u>

This document was generated on 04/17/2015

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**