


SPECIFICATIONS				
CONTACT CARRIER MATERIAL	NYLON OR TPU			
MOLDED HEAD MATERIAL/COLOR	TPU/YELLOW			
CONTACT MATERIAL/PLATING	BRASS/GOLD			
COUPLING NUT MATERIAL/PLATING	BRASS/NICKEL			
RATED CURRENT [A]	4.0 A			
RATED VOLTAGE [V]	250 V			
OUTER JACKET MATERIAL/COLOR	PVC/GRAY			
CONDUCTOR INSULATION MATERIAL	PVC			
NUMBERS OF CONDUCTORS [AWG]	5x22 AWG			
TEMPERATURE RANGE	-40°C to +105°C (-40°F to +221°F)			
PROTECTION CLASS	NEMA 1,3,4,6P AND IEC IP68, IP69K			



CABLE LENGTH	TOLERANCE *					
ALL LENGTHS	+ 4% (OR 50mm) OF LENGTH - 0% (OR 0mm) OF LENGTH WHICHEVER IS GREATER					
STRIP LENGTH	TOLERANCE *					
0-7mm	±0.5mm					
8-29mm	±1.0mm					
30-49mm	±2.0mm ±3.0mm					
50-69mm						
70-100mm	±4.0mm					
OVER 100mm	±5.0mm					
* UNILESS OTHERWISE SPECIFIED						

CBM 04/06/11 3397

DATE

NOTES:

REV DESCRIPTION

1. "*" INDICATES CABLE LENGTH IN METERS. CONTACT TURCK TO ORDER SPECIFIC LENGTHS.

E DRAWING PROCESSED AS PART OF ECO 33971

	RELATED DOCUMENTS 1. 2. 3. 4.		3RD ANGLE PROJECTION	THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.	High Technology Sensors and Automation Controls MINNEAPOLIS, 1-800-54 (763) 553 turck.c		3000 CAMPUS MINNEAPOLIS, MN 1-800-544-7 (763) 553-7 (763) 553-0 turck.com	55441 7769 300 708 fax
		MATERIAL		DRFT CBM	DATE 10/09/00	DESCRIPTION RK 4.5T-*-	DC 4 ET	
		SEE SPECIFICATIONS	ALL DIMENSIONS DISPLAYED ON THIS	DSGN	SCALE 1 = 1.0		113 4.31	
			DRAWING ARE FOR REFERENCE ONLY	UNIT OF MEASUREMENT		IDENTIFICATION NO.		REV
		FINISH		AAU I IAAETE	ER[INCH]	IDENTIFICATION NO.		KEV
1	33971	SEE SPECIFICATIONS	CONTACT TURCK FOR MORE INFORMATION	MILLIMETE				Ł
Ī	ECO NO.			DO NOT SCALE	THIS DRAWING	FILE: 777000630	SHEET	1 OF 1

SOURCE DRAWING - FOR REFERENCE ONLY