

Tools

ECO Series TECHNO LABORATORY DRILLS

TECHNO 003 MR



TECHNO 003 R



Model	TECHNO 003 MR	TECHNO 003 R	TECHNO 003 MRE
Adjustable rotation speed	11000 à 37000 rpm	11000 à 37000 rpm	11000 à 37000 rpm
Capacity	Ø 0.2 à 3.2 mm	Ø 0.2 à 3.2 mm	0,2 à 3,2 mm
Swan neck	120 mm	170 mm	120 mm
Work table	250 x 150 mm	380 x 295 mm	250 x 150 mm
Spindle travel	6 mm	6 mm	6 mm
Low voltage lighting	Yes	Yes	No
Dust removal connection	Yes	Yes	No
External dimensions	250 x 150 x 260 mm	380 x 295 x 260 mm	250 x 150 x 260 mm
Weight	4 kg	5 kg	3,8 kg
Spindle output	115 W	115 W	115 W
Electrical connection	220 /240 V - 50/60 Hz	220/240 - 50/60 Hz	220/240 V - 50/60 Hz
Code	DP 593	EP 503	DP 595

TECHNO 001



TECHNO 002



Model	TECHNO 001	TECHNO 002
Adjustable rotation speed	8000 à 20000 rpm	20000 rpm
Capacity	Ø 0.2 à 3.2 mm	Ø 0.2 à 3.2 mm
Swan neck	175 mm	150 mm
Work table	285 x 245 mm	300 x 245 mm
Spindle travel	25 mm	15 mm
Automatic clamping chuck	Ø 0.2 à 3.2 mm	Ø 0.2 à 3.2 mm
Low voltage lighting	Yes	Yes
Dust removal connection	Yes	Yes
External dimensions	395 x 245 x 230 mm	395 x 245 x 250 mm
Weight	8,5 kg	5 kg
Spindle output	130 W	24 V/30 W
Electrical connection	220/240 V - 50/60 Hz	220/240 V - 50/60 Hz
Code	EP 501	EP 502



© Circuit Imprimé Français - Technical conception : [France Cybermedia](http://www.cif.fr/uk/ukp40.shtml) -