

Terminal Repositionable Vinyl Cloth Material (B-498)

Specially designed narrow-width markers automatically set to fixed spacing and separation between leg ends and automatically rotate to top-down orientation for perfect alignment on terminal blocks. Temp Range -40°F to 175°F (-40°C to 80°C), UL Recognized




Figure 30




Diagram	Catalog #	B#	Material	Color	Width of Strip Inch (mm)	Label Width A Inch (mm)	Roll Length B Inch (mm)	Labels/Roll
B-498 Repositionable Vinyl Cloth Labels								
Fig. 30	XC-240-498	B-498	Vinyl Cloth	BK on WT	0.240 (6.1) wide	0.240 (6.1)	20 ft. (7.9 m)	1 roll (cont.)
Fig. 30	XC-318-498	B-498	Vinyl Cloth	BK on WT	0.318 (8.1) wide	0.318 (8.1)	20 ft. (7.9 m)	1 roll (cont.)
Fig. 30	XC-375-498	B-498	Vinyl Cloth	BK on WT	0.375 (9.5) wide	0.375 (9.5)	20 ft. (7.9 m)	1 roll (cont.)

Polyester Labels (B-422)

Permanent adhesive, good for powder-coated/textured surfaces making it ideal for pat panels, outlets and faceplate identification. Best on flat surfaces. Temp. Range: -40°F to 212°F (-40°C to 100°C). UL recognized.




Figure 29




Figure 59



Diagram	Catalog #	B#	Material	Color	Sized To Fit	Label Width A Inch (mm)	Label Height B Inch (mm)	Labels/Roll
B-422 Polyester Labels								
Fig. 59	XC-375-422	B-422	Polyester	BK on WT	Label Punch Blocks or Multiple Ports on Cont. Tape	0.375 (9.530)	30 ft. (9.140 m)	1 roll (cont.)
Fig. 59	XC-475-422	B-422	Polyester	BK on WT	Label Punch Blocks or Multiple Ports on Cont. Tape	0.475 (12.070)	30 ft. (9.140 m)	1 roll (cont.)
Fig. 29	X-7-422	B-422	Polyester	BK on WT	Label Each Port	0.500 (12.700)	0.500 (12.700)	350
Fig. 29	X-17-422	B-422	Polyester	BK on WT	Label Faceplate	1.000 (25.400)	0.500 (12.700)	500
Fig. 29	X-29-422	B-422	Polyester	BK on WT	Label Faceplate	1.500 (38.100)	0.500 (12.700)	500

Racks, Bays, Frames, Public Network & Data Center ID (B-422, B-483, B-595)

B-422 Polyester Material - Permanent adhesive, good for powder-coated/textured surfaces. Best on flat surfaces. Temp. Range: -40°F to 212°F (-40°C to 100°C). UL recognized.

B-483 Polyester Material - Permanent adhesive for powder-coated/textured surfaces. Best on flat surfaces Temp. Range: -40°F to 248°F (-40°C to 120°C). UL recognized.

B-595 Indoor/Outdoor Vinyl Material - Permanent adhesive, very pliable, good for rough surfaces and outdoor use, wide range of colors. Temp. Range: -40°F to 248°F (-40°C to 120°C). UL recognized.




Figure 29



Figure 33



Diagram	Catalog #	B#	Material	Color	Label Width A Inch (mm)	Label Height B Inch (mm)	Labels/Roll
B-422 Polyester Labels							
Fig. 29	X-17-422	B-422	Polyester	BK on WT	1.000 (25.4)	0.500 (12.7)	500
Fig. 29	X-29-422	B-422	Polyester	BK on WT	1.500 (38.1)	0.500 (12.7)	500
Fig. 29	X-30-422	B-422	Polyester	BK on WT	1.500 (38.1)	0.750 (19.1)	250
Fig. 29	X-19-422	B-422	Polyester	BK on WT	1.000 (25.4)	1.000 (25.4)	250
Fig. 33	XC-1000-422	B-422	Polyester	BK on WT	1.000 (25.4)	30 ft. (9.1 m)	1 roll (cont.)
B-483 Polyester Labels							
Fig. 29	X-17-483	B-483	Polyester	BK on WT	1.000 (25.4)	0.500 (12.7)	500
Fig. 29	X-61-483	B-483	Polyester	BK on WT	2.000 (50.8)	0.500 (12.7)	100
Fig. 29	X-20-483	B-483	Polyester	BK on WT	2.000 (50.8)	1.000 (25.4)	100
B-595 Indoor/Outdoor Vinyl Film							
Fig. 33	XC-500-595-YL-BK	B-595	Vinyl	BK on YL*	0.500 (12.7)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-1000-595-YL-BK	B-595	Vinyl	BK on YL*	1.000 (25.4)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-1500-595-YL-BK	B-595	Vinyl	BK on YL*	1.500 (38.1)	30 ft. (9.1 m)	1 roll (cont.)

*Red, Orange, Green, Blue, White, and Clear are also available on page page 339.

