

About LabfacilityFormed in 1971, Labfacility
specialize in the field of

Temperature and Process

We are the largest UK manufacturer of both

temperature sensors and

thermocouple connectors

Quality & Service

of Labfacility.

available from our

accreditation.

Quality and Service are key

elements in the continued growth

Technical support is always freely

experienced technical sales teams and the company has ISO9001

Measurement.

LABFACILITY

TEMPERATURE & PROCESS TECHNOLOGY

Miniature Quick Wire plug



'Just push-in wire & tighten screw'

- These quick connect versions allow rapid termination
 - Miniature connector with flat plug pins
 - Easy 'jab-in' connection for rapid termination, Just push-in wire & tighten screw
 - Contacts are polarised to prevent incorrect connection
 - Available in Thermocouple types K, J, T, E, N, R/S & Copper
 - For Types K, J, T, E & N contacts are made from true Thermocouple alloys
 - R/S type has compensating copper/copper nickel alloy contacts
 - Colour coded in accordance with IEC specification
 - Maximum continuous temperature 220 deg°C

T/C Type	Colour Code (IEC)	+Positive Contact (alloy type)	-Negative Contact (alloy type)	Part Code	Farnell Order Code
K	Green	+Nickel Chromium	-Nickel Alloy	IM-K-MQ	381-0392
J	Black	+Iron	-Copper Nickel	IM-J-MQ	381-0380
Т	Brown	+Copper	-Copper Nickel	IM-T-MQ	381-0410
Copper	White	+Copper	-Copper	IM-CU-MQ	381-0422
В	Grey	+Copper	-Copper	IM-B-MQ	234-7024
E	Violet	+Nickel Chromium	-Copper Nickel	IM-E-MQ	234-7025
N	Pink	+Nickel/Chro/Silicon	-Nickel Silicon	IM-N-MQ	234-7026
R/S	Orange	+Copper	-Copper Alloy	IM-R/S-MQ	234-7028

Contact Details

Website
www.labfacility.com

Email sales@labfacility.com



