



LABFACILITY
TEMPERATURE & PROCESS TECHNOLOGY

IEC Mineral Insulated Thermocouple with Standard Plug

About Labfacility

Formed in 1971, Labfacility specialize in the field of Temperature and Process Measurement.

We are the largest UK manufacturer of both temperature sensors and thermocouple connectors

Quality & Service


Quality and Service are key elements in the continued growth of Labfacility.

Technical support is always freely available from our experienced technical sales teams and the company has ISO9001 accreditation.

Contact Details

Email
sales@labfacility.com

Website
www.labfacility.com



- ◆ Mineral insulated Type 'K' Thermocouple
- ◆ 310 stainless steel sheath
- ◆ Highly flexible, sheath can be bent/formed to suit many applications and processes
- ◆ diameters include 1.5, 3.0 & 6.0mm
- ◆ Insulated hot junction
- ◆ Probe temperature range -40°C up to +1100°C
- ◆ Standard plug termination (200°C)
- ◆ Conforms to IEC specification

Specifications

Sensor type:	Type 'K' with Nickel Chromium/Nickel Aluminium conductors
Construction:	Flexible mineral insulated probe, 310 stainless steel sheath & standard plug termination
Sheath composition:	310 stainless steel (25/20 chromium nickel steel)
Element/hot junction:	Single element, junction insulated from sheath in order to prevent electrical noise & interference
Termination:	Standard round pin plug, colour coded 'Green in accordance IEC
Reference Tables/Tolerance:	In accordance with IEC
Probe temperature range:	-40°C to +1100°C
Plug temperature range:	200°C



About Labfacility

Formed in 1971, Labfacility specialize in the field of Temperature and Process Measurement.

We are the largest UK manufacturer of both temperature sensors and thermocouple connectors.

Quality & Service

Quality and Service are key elements in the continued growth of Labfacility.

Technical support is always freely available from our experienced technical sales teams and the company has ISO9001 accreditation.

Contact Details

Email
sales@labfacility.com

Website
www.labfacility.com

310 stainless steel

Good corrosion & oxidation resistance to suit a wide range of processes, satisfactorily operates in sulphur bearing atmospheres.

Typical applications include brick & cement kilns, glass industry, heat treatment & annealing furnaces, power stations, flues, heat exchangers etc.

Order codes:

T/C Type	Probe Dia. (mm)	Probe Length (mm)	Sheath	Manufacturing Part No.	Farnell code
K	1.5	500	310SS	MB-ISK-S15-500-SP	242-0274
K	1.5	1000	310SS	MB-ISK-S15-1000-SP	242-0273
K	1.5	2000	310SS	MB-ISK-S15-2000-SP	128-9609
K	3	500	310SS	MB-ISK-S30-500-SP-I	242-0280
K	3	1000	310SS	MB-ISK-S30-1000-SP	242-0279
K	6	500	310SS	MB-ISK-S60-500-SP	242-0271
K	6	1000	310SS	MB-ISK-S60-1000-SP	242-0270