



Thermocouple Cable PFA Insulated Twin Twisted Pair



About Labfacility

Formed in 1971, Labfacility specialize in the field of Temperature and Process Measurement.

We are the largest UK manufacturer of both temperature sensors and thermocouple connectors

Quality & Service

Quality and Service are key elements in the continued growth of Labfacility.

Technical support is always freely available from our experienced technical sales teams and the company has ISO9001 accreditation.

Contact Details

Email
sales@labfacility.com

Website
www.labfacility.com

- ◆ PFA Teflon® twin twisted pair for extending or making simple thermocouples
- ◆ Single pair of PFA insulated conductors twisted together
- ◆ Good mechanical strength and flexibility, resistant to oils, acids and other adverse fluids, gasses, steam & pressure etc.
- ◆ Thermocouple types K & T
- ◆ 50 & 100 metre reel lengths
- ◆ Tolerance Class 1 for optimum accuracy
- ◆ Insulation rating -75°C to 260°C
- ◆ Colour coded to IEC-584-3

T/C Type	Conductors	Cores	Reel Length	Manufacturers Part No.	Farnell Order Code
K	1/0.2mm	+Green/-White	50 metres	WK-203-D-50M	208-1277
K	1/0.2mm	+Green/-White	100 metres	WK-203-D-100M	208-1278
T	1/0.2mm	+Brown/-White	50 metres	WT-304-D-50M	208-1273
T	1/0.2mm	+Brown/-White	100 metres	WT-304-D-100M	208-1274
K	1/0.315mm	+Green/-White	50 metres	WK-204-D-50M	208-1279
T	1/0.315mm	+Brown/-White	50 metres	WT-306-D-50M	208-1275
K	7/0.2mm	+Green/-White	50 metres	XS-752-D-50M	208-1280
T	7/0.2mm	+Brown/-White	50 metres	XF-566-FAR	208-1276