



## IEC Type J Mineral Insulated Thermocouple with Miniature Plug

### About Labfacility

Formed in 1971, Labfacility specialize in the field of Temperature and Process Measurement.

We are the largest UK manufacturer of both temperature sensors and thermocouple connectors

### Quality & Service

Quality and Service are key elements in the continued growth of Labfacility.

Technical support is always freely available from our experienced technical sales teams and the company has ISO9001 accreditation.

### Contact Details

Email  
sales@labfacility.com

Website  
www.labfacility.com



- ◆ Mineral insulated Type 'J' Thermocouple
- ◆ 310 stainless steel sheath
- ◆ Highly flexible, sheath can be bent/formed to suit many applications and processes
- ◆ 1.0 & 1.5mm diameters
- ◆ Insulated hot junction
- ◆ Probe temperature range -40°C up to +750C
- ◆ Miniature plug termination (200°C)
- ◆ Conforms to IEC specification

### Specifications

Sensor type:	Type 'J'
Construction:	Flexible mineral insulated probe with 310 stainless steel sheath
Element/hot junction:	Single element, junction insulated from sheath (offers protection against spurious electrical signals)
Termination:	Miniature flat pin plug, colour coded 'Black' in accordance IEC
Probe temperature range:	-40°C to +750°C
Plug temperature range:	200°C

### 310 stainless steel

Good corrosion & oxidation resistance to suit a wide range of processes, satisfactorily operates in sulphur bearing atmospheres.

Typical applications include brick & cement kilns, glass industry, heat treatment & annealing furnaces, power stations, flues, heat exchangers etc.

### Order codes:

T/C Type	Probe	Probe Dia. (mm)	Sheath Length (mm)	Manufacturing Part No.	Farnell code
J	1.0	250	310SS	MB-ISJ-S10-250-MP	245-4346
J	1.5	500	310SS	MB-ISJ-S15-500-MP	245-4347
J	1.5	1000	310SS	MB-ISJ-S15-1000-MP	245-4348