


Metal Film Resistors, High Precision, High Stability



FEATURES

- Extremely low temperature coefficient of resistance
- Very low noise and voltage coefficient
- Very good high frequency characteristics
- Can replace wirewound bobbins
- Proprietary epoxy coating provides superior moisture protection
- For surface mount product, see Vishay Dale's PSF datasheet (www.vishay.com/doc?30162)
- Material categorization: For definitions of compliance please see www.vishay.com/doc?99912



RoHS* COMPLIANT

Note

* Lead (Pb)-containing terminations are not RoHS-compliant. Exemptions may apply.

STANDARD ELECTRICAL SPECIFICATIONS						
GLOBAL MODEL	HISTORICAL MODEL	POWER RATING ⁽³⁾ P _{85 °C} W	LIMITING ELEMENT VOLTAGE MAX. ⁽¹⁾ V	TEMPERATURE COEFFICIENT ± ppm/°C	TOLERANCE ± %	RESISTANCE RANGE Ω
PTF51	PTF-51	0.05	200	5, 10, 15	0.02, 0.05, 0.1, 0.25, 0.5, 1	15 to 100K
PTF56	PTF-56	0.125	300	5, 10, 15	0.01, 0.02, 0.05, 0.1, 0.25, 0.5, 1	15 to 500K
PTF65	PTF-65	0.25	500	5, 10, 15	0.05, 0.1, 0.25, 0.5, 1	15 to 1M

Notes

- DSCC has created a drawing to support the need for a precision axial-leaded product. Vishay Dale is listed as a resource on this drawing as follows:

DSCC DRAWING NUMBER	VISHAY DALE MODEL	POWER RATING P _{85 °C} W	RESISTANCE RANGE Ω	TOLERANCE ± %	TEMPERATURE COEFFICIENT ± ppm/°C	MAXIMUM WORKING VOLTAGE ⁽¹⁾ V
89088	PTF56..31, PTF56..32 ⁽²⁾	0.100	15 to 100K	0.01, 0.05, 0.1, 0.5, 1	5, 10	200
90038	PTF65..16, PTF65..14 ⁽²⁾	0.250	15 to 100K	0.05, 0.1, 0.5, 1	5, 10	200

This drawing can be viewed at: www.landandmaritime.dla.mil/Programs/MilSpec/ListDwg.aspx?DocTYPE=DSCCdwg

- ⁽¹⁾ Continuous working voltage shall be $\sqrt{P \times R}$ or maximum working voltage, whichever is less.
- ⁽²⁾ Hot solder dipped leads.
- ⁽³⁾ For operation of the PTF resistors at higher power ratings, see the Load Life Shift Due to Power and Derating table. This table gives a summary of the effects of using the PTF product at the more common combinations of power rating and case size, as well as quantifies the load life stability under those conditions.


TEMPERATURE COEFFICIENT CODES		
GLOBAL TC CODE	HISTORICAL TC CODE	TEMPERATURE COEFFICIENT
Z	T-16	5 ppm/°C
Y	T-13	10 ppm/°C
X	T-10	15 ppm/°C

GLOBAL PART NUMBER INFORMATION																																						
New Global Part Numbering: PTF5620K500BYRE (preferred part numbering format)																																						
<div style="display: flex; justify-content: space-around; font-weight: bold; font-size: 1.2em;"> P T F 5 6 2 0 K 5 0 0 B Y R E </div>																																						
<table border="1"> <tr><th>GLOBAL MODEL</th></tr> <tr><td>PTF51</td></tr> <tr><td>PTF56</td></tr> <tr><td>PTF65</td></tr> </table>	GLOBAL MODEL	PTF51	PTF56	PTF65	<table border="1"> <tr><th>RESISTANCE VALUE</th></tr> <tr><td>R = Ω</td></tr> <tr><td>K = kΩ</td></tr> <tr><td>M = MΩ</td></tr> <tr><td>15R000 = 15 Ω</td></tr> <tr><td>500K00 = 500 kΩ</td></tr> <tr><td>1M0000 = 1.0 MΩ</td></tr> </table>	RESISTANCE VALUE	R = Ω	K = kΩ	M = MΩ	15R000 = 15 Ω	500K00 = 500 kΩ	1M0000 = 1.0 MΩ	<table border="1"> <tr><th>TOLERANCE CODE</th></tr> <tr><td>T = ± 0.01 % ⁽⁴⁾</td></tr> <tr><td>Q = ± 0.02 % ⁽⁴⁾</td></tr> <tr><td>A = ± 0.05 %</td></tr> <tr><td>B = ± 0.1 %</td></tr> <tr><td>C = ± 0.25 %</td></tr> <tr><td>D = ± 0.5 %</td></tr> <tr><td>F = ± 1 %</td></tr> </table>	TOLERANCE CODE	T = ± 0.01 % ⁽⁴⁾	Q = ± 0.02 % ⁽⁴⁾	A = ± 0.05 %	B = ± 0.1 %	C = ± 0.25 %	D = ± 0.5 %	F = ± 1 %	<table border="1"> <tr><th>TEMP. COEFFICIENT</th></tr> <tr><td>Z = 5 ppm</td></tr> <tr><td>Y = 10 ppm</td></tr> <tr><td>X = 15 ppm</td></tr> <tr><td>0 = Special</td></tr> </table>	TEMP. COEFFICIENT	Z = 5 ppm	Y = 10 ppm	X = 15 ppm	0 = Special	<table border="1"> <tr><th>PACKAGING</th></tr> <tr><td>EK = Lead (Pb)-free, bulk</td></tr> <tr><td>EA = Lead (Pb)-free, T/R (full)</td></tr> <tr><td>EB = Lead (Pb)-free, T/R (1000 pieces)</td></tr> <tr><td>BF = Tin/lead, bulk</td></tr> <tr><td>RE = Tin/lead, T/R (full)</td></tr> <tr><td>R6 = Tin/lead, T/R (1000 pieces)</td></tr> </table>	PACKAGING	EK = Lead (Pb)-free, bulk	EA = Lead (Pb)-free, T/R (full)	EB = Lead (Pb)-free, T/R (1000 pieces)	BF = Tin/lead, bulk	RE = Tin/lead, T/R (full)	R6 = Tin/lead, T/R (1000 pieces)	<table border="1"> <tr><th>SPECIAL</th></tr> <tr><td>Blank = Standard (Dash number) (Up to 3 digits) From 1 to 999 as applicable</td></tr> </table>	SPECIAL	Blank = Standard (Dash number) (Up to 3 digits) From 1 to 999 as applicable
GLOBAL MODEL																																						
PTF51																																						
PTF56																																						
PTF65																																						
RESISTANCE VALUE																																						
R = Ω																																						
K = kΩ																																						
M = MΩ																																						
15R000 = 15 Ω																																						
500K00 = 500 kΩ																																						
1M0000 = 1.0 MΩ																																						
TOLERANCE CODE																																						
T = ± 0.01 % ⁽⁴⁾																																						
Q = ± 0.02 % ⁽⁴⁾																																						
A = ± 0.05 %																																						
B = ± 0.1 %																																						
C = ± 0.25 %																																						
D = ± 0.5 %																																						
F = ± 1 %																																						
TEMP. COEFFICIENT																																						
Z = 5 ppm																																						
Y = 10 ppm																																						
X = 15 ppm																																						
0 = Special																																						
PACKAGING																																						
EK = Lead (Pb)-free, bulk																																						
EA = Lead (Pb)-free, T/R (full)																																						
EB = Lead (Pb)-free, T/R (1000 pieces)																																						
BF = Tin/lead, bulk																																						
RE = Tin/lead, T/R (full)																																						
R6 = Tin/lead, T/R (1000 pieces)																																						
SPECIAL																																						
Blank = Standard (Dash number) (Up to 3 digits) From 1 to 999 as applicable																																						
Historical Part Number example: PTF-5620K5BT-13R36 (will continue to be accepted)																																						
PTF-56		20K5		B																																		
T-13		R36																																				
HISTORICAL MODEL	RESISTANCE VALUE	TOLERANCE CODE	TEMP. COEFFICIENT	PACKAGING																																		

Notes

- For additional information on packaging, refer to the Through-Hole Resistor Packaging document (www.vishay.com/doc?31544).
- ⁽⁴⁾ Historical tolerance codes were BB for 0.01 % and BC for 0.02 %.

TECHNICAL SPECIFICATIONS				
PARAMETER	UNIT	PTF51	PTF56	PTF65
Rated Dissipation at 85 °C	W	0.05	0.125	0.25
Limiting Element Voltage	V_{\equiv}	200	300	500
Insulation Voltage (1 Min)	V_{eff}	> 500	> 500	> 500
Thermal Resistance	K/W	< 1300	< 520	260
Terminal Strength, Axial	N	> 150	> 50	> 50
Insulation Resistance	Ω	$\geq 10^{11}$	$\geq 10^{11}$	$\geq 10^{11}$
Category Temperature Range	°C	- 55 to + 150	- 55 to + 150	- 55 to + 150
Failure Rate	$10^{-9}/h$	< 1	< 1	< 1
Weight (Max.)	g	0.11	0.35	0.75

DIMENSIONS


GLOBAL MODEL	DIMENSIONS in inches (millimeters)			
	L	D	L _{1 max.}	d
PTF51	0.150 ± 0.020 (3.81 ± 0.51)	0.070 ± 0.010 (1.78 ± 0.25)	0.200 (5.08)	0.016 (0.41)
PTF56	0.250 ± 0.031 (6.35 ± 0.79)	0.091 ± 0.009 (2.31 ± 0.23)	0.300 (7.62)	0.025 (0.64)
PTF65	0.375 ± 0.062 (9.53 ± 1.57)	0.145 ± 0.016 (3.68 ± 0.41)	0.475 (12.07)	0.025 (0.64)

Note

- (1) Lead length for product in bulk pack. For product supplied in tape and reel, the actual lead length would be based on the body size, tape spacing and lead trim.

PERFORMANCE		
TEST	CONDITIONS OF TEST	TEST RESULTS (TYPICAL TEST LOTS)
Life (at Standard Power Ratings)	MIL-PRF-55182 Paragraph 4.8.18 1000 h rated power at + 85 °C	$\leq \pm 0.04$ %
Thermal Shock	Mil-STD-202, Method 107 - 55 °C to + 85 °C	$\leq \pm 0.02$ %
Short Time Overload	MIL-R-10509, Paragraph 4.7.6	$\leq \pm 0.01$ %
Low Temperature Operation	MIL-PRF-55182, Methods 4.8.10	$\leq \pm 0.02$ %
Moisture	MIL-PRF-55182, Paragraph 4.8.15	$\leq \pm 0.08$ %
Resistance to Soldering Heat	MIL-STD-202, Methods 210	$\leq \pm 0.02$ %
Damp Heat IEC 60068-2-3	56 days at 40 °C and 92 % RH	$\leq \pm 0.08$ %
Dielectric Withstanding Voltage	MIL-STD-202, Methods 301 and 105	$\leq \pm 0.01$ %

MATERIAL SPECIFICATIONS	
Element	Precision deposited nickel chrome alloy with controlled annealing
Encapsulation	Specially formulated epoxy compounds. Coated construction
Core	Fire-cleanded high purity ceramic
Termination	Standard lead material is solder-coated copper. Solderable and weldable per MIL-STD-1276, Type C.


MARKING			
Temperature coefficient: T10 = 15 ppm, T13 = 10 ppm, T16 = 5 ppm			
Tolerance: F = 1 %, D = 0.5 %, C = 0.25 %, B = 0.1 %, A = 0.05 %, BC = 0.02 %, BB = 0.01 %			
PTF51: (3 lines)		PTF56, PTF65: (4 lines)	
PTF51	Style and size	PTF56	Style and size
37K4	Value	49K9	Value
BC T13	Tolerance and TC	BB T16	Tolerance and TC
		1211	4-digit date code

LOAD LIFE SHIFT DUE TO POWER AND DERATING (AT 85 °C)


The power rating for the PTF parts is tied to the derating temperature, the heat rise of the parts, and the ΔR for the load life performance. When the tables/graphs below are used together they show that when the parts are run at higher power ratings, the parts will run hotter, which has the potential of causing the resistance of the parts to shift more over the life of the part.

LOAD LIFE SHIFT VS. POWER RATING

LOAD LIFE	CONDITIONS OF TEST	MAXIMUM ΔR (TYPICAL TEST LOTS)			
	MIL-PRF-55182 Paragraph 4.8.18 1000 h rated power at + 85 °C	≤ ± 0.04 %	≤ ± 0.15 %	≤ ± 0.5 %	≤ ± 1.0 %
MODEL		POWER RATING AT + 85 °C			
PTF51		1/20 W	1/10 W	1/8 W	1/4 W
PTF56		1/8 W	-	1/4 W	1/2 W
PTF65		1/4 W	-	1/2 W	3/4 W



DERATING



THERMAL RESISTANCE

Example: When a PTF56 part is run at 1/8 W in a 70 °C ambient environment, the resistor will generate enough heat that the surface temperature of the part will reach about 17 °C over the ambient temperature, and over the life of the part this could cause the resistance value to shift up to ± 0.04 %.

If the same resistor was instead run at 1/4 W in a 70 °C environment, the element will heat up to about 30 °C over ambient, and over the life of the part the resistance value could shift roughly ± 0.5 %.


And if the resistor was run at its maximum power rating of 1/2 W in a 70 °C environment, it will heat up to about 61 °C over ambient, and you could see the resistance value shift roughly ± 1 % over the life of the part.

TEMPERATURE COEFFICIENT OF RESISTANCE

Temperature coefficient (TC) of resistance is normally stated as the maximum amount of resistance change from the original + 25 °C value as the ambient temperature increases or decreases. This is most commonly expressed in parts per million per degree centigrade (ppm/°C).

The resistance curve over the operating temperature range is usually a non-linear curve within predictable maximum limits. PTF resistors have a very uniform resistance temperature characteristic when measured over the operating range of - 20 °C to + 85 °C. The standard temperature coefficients available are X = ± 15 ppm/°C, Y = ± 10 ppm/°C and Z = ± 5 ppm/°C.

Some applications of the PTF require operation beyond the specifications of - 20 °C to + 85 °C. The change in temperature coefficient of resistance is very small (less than ± 0.05 ppm/°C) over the expanded temperature range of - 55 °C to + 150 °C. Therefore, when operating outside the range - 20 °C to + 85 °C, the designer can plan for a worst case addition of ± 0.05 ppm/°C for each degree centigrade beyond either - 20 °C or + 85 °C as indicated in the graph. This applies to all three temperature coefficient codes.



Example: Assume the operating characteristics demand a temperature range from - 55 °C to + 125 °C. This requires a ± 35 °C Δ below - 20 °C and a ± 40 °C Δ above + 85 °C. The extreme Δ being ± 40 °C means that the worst case addition to the specified TC limit of ± 0.05 ppm/°C times ± 40 °C or ± 2 ppm/°C. Therefore, a Z which is characterized by a base TC limit of ± 5 ppm/°C over the temperature range of - 20 °C to + 85 °C will exhibit a maximum temperature coefficient of ± 7 ppm/°C over the expanded portion of the temperature range of - 55 °C to + 125 °C.



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.