

ALUMINUM ELECTROLYTIC CAPACITORS

nichicon

ZG

3.95mmL MAX. Chip Type,
Wide Temperature Range
series



For SMD




Smaller



Anti-Solvent
Feature


- Chip type with 3.95mmLMAX height. Operating over wide temperature range of -40 to $+105^{\circ}\text{C}$.
- Designed for surface mounting on high density PC board.
- Applicable to automatic mounting machine fed with carrier tape.
- Compliant to the RoHS directive (2011/65/EU).



Specifications


Item	Performance Characteristics							
Category Temperature Range	-40 to +105°C							
Rated Voltage Range	6.3 to 50V							
Rated Capacitance Range	0.1 to 100μF							
Capacitance Tolerance	±20% at 120Hz, 20°C							
Leakage Current	After 2 minutes' application of rated voltage, leakage current is not more than 0.01 CV or 3 (μA) , whichever is greater.							
Tangent of loss angle (tan δ)	Rated voltage (V)	6.3	10	16	25	35	50	120Hz 20°C
	tan δ (MAX.)	0.38	0.32	0.20	0.16	0.14	0.14	
Stability at Low Temperature	Rated voltage (V)	6.3	10	16	25	35	50	120Hz
	Impedance ratio	Z-25°C / Z+20°C	6	5	3	3	3	
	ZT / Z20 (MAX.)	Z-40°C / Z+20°C	10	10	6	6	4	
Endurance	The specifications listed at right shall be met when the capacitors are restored to 20°C after the rated voltage is applied for 1000 hours at 105°C.				Capacitance change		Within ±30% of the initial capacitance value	
					tan δ		300% or less than the initial specified value	
					Leakage current		Less than or equal to the initial specified value	
Shelf Life	After storing the capacitors under no load at 105°C for 1000 hours and then performing voltage treatment based on JIS C 5101-4 clause 4.1 at 20°C, they shall meet the specified values for the endurance characteristics listed above.							
Resistance to soldering heat	The capacitors are kept on a hot plate for 30 seconds, which is maintained at 250°C. The capacitors shall meet the characteristic requirements listed at right when they are removed from the plate and restored to 20°C.				Capacitance change		Within ±10% of the initial capacitance value	
					tan δ		Less than or equal to the initial specified value	
					Leakage current		Less than or equal to the initial specified value	
Marking	Black print on the case top.							

Chip Type



Voltage	V	6.3	10	16	25	35	50
Code	j	A	C	E	V	H	

Type numbering system (Example : 16V 10 μF)



Dimensions

V		6.3	10	16	25	35	50
Cap. (μF)	Code	0J	1A	1C	1E	1V	1H
0.1	0R1						4 0.9
0.22	R22						4 2.2
0.33	R33						4 2.8
0.47	R47						4 3.3
1	010						4 5.4
2.2	2R2						4 9.6
3.3	3R3						4 12
4.7	4R7				4 11	4 13	5 16
10	100			4 16	5 20	5 22	6.3 26
22	220	4 19	5 24	5 26	6.3 33	6.3 36	
33	330	5 26	5 30	6.3 35	6.3 42		
47	470	5 32	6.3 40	6.3 44			
100	101	6.3 52					Case size φD (mm) Rated ripple

Rated ripple current (mA rms) at 105°C 120Hz

Frequency coefficient of rated ripple current

Frequency	50 Hz	120 Hz	300 Hz	1 kHz	10 kHz or more
Coefficient	0.70	1.00	1.17	1.36	1.50

- Taping specifications are given in page 23.
- Recommended land size soldering by reflow are given in page 18,19.
- Please refer to page 3 for the minimum order quantity.

CAT.8100D