


1585LC Multi-Conductor - Category 5e Nonbonded-Pair Cable



For more Information
please call

1-800-Belden1



General Description:

CAT5e (200MHz), 4-Pair, U/UTP-Unshielded, Limited Combustible FHC 25/50, Plenum-CMP, Premise Horizontal Cable, 24 AWG Solid Bare Copper Conductors, FEP Insulation, FEP Jacket

Usage (Overall)

Suitable Applications: Premise Horizontal Cable, Gigabit Ethernet, 100BaseTX, 100BaseVG ANYLAN, 155ATM, 622ATM, NTSC/PAL Component or Composite Video, AES/EBU, Digital Video, RS-422

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material
4	24	Solid	BC - Bare Copper

Total Number of Conductors: 8

Insulation

Insulation Material:

Insulation Trade Name	Insulation Material
Teflon®	FEP - Fluorinated Ethylene Propylene

Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
FEP - Fluorinated Ethylene Propylene

Outer Jacket Diameter:

Nom. Dia. (mm)
4.674

Outer Jacket Ripcord: No

Pair

Pair Color Code Chart:

Number	Color
1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange
3	White/Green Stripe & Green
4	White/Brown Stripe & Brown

Mechanical Characteristics (Overall)

Operating Temperature Range: -40°C To +150°C

Bulk Cable Weight: 37.205 Kg/Km

Max. Recommended Pulling Tension: 155.687 N

Min. Bend Radius/Minor Axis: 25.400 mm

Min. Bend/Installation: 45.720 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification: CMP, FHC 25/50

NEC Articles: NFPA 259, NFPA 255

CEC/C(UL) Specification: CMP, FHC 25/50

EU Directive 2011/65/EU (ROHS II): Yes

1585LC Multi-Conductor - Category 5e Nonbonded-Pair Cable

Other Standards:	ISO/IEC 11801 ed 2.1 (2008) Class D
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Telecommunications Standards:	Category 5e - TIA 568.C.2
Other Specification:	NEMA WC-63.1 Category 5e

Flame Test

UL Flame Test:	NFPA 262 Plenum Flame Test (UL910)(FT6), UL723 (NFPA 255)
C(UL) Flame Test:	Limited Smoke
CSA Flame Test:	FT6, Limited Smoke

Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Suitability - Aerial:	Yes - UL
Suitability - Burial:	No

Plenum/Non-Plenum

Plenum (Y/N):	Yes
Plenum Number:	1585A
Non-Plenum Number:	1583A

Electrical Characteristics (Overall)

Nom. Mutual Capacitance:

Capacitance (pF/m)
49.215

Maximum Capacitance Unbalance (pF/100 m): 330

Nominal Velocity of Propagation:

VP (%)
72

Maximum Delay:

Delay (ns/100 m)
510 @ 100MHz

Max. Delay Skew:

Delay Skew (ns/100 m)
45

Maximum Conductor DC Resistance:

DCR @ 20°C (Ohm/100 m)
9.38

Max. Operating Voltage - UL:

Voltage
300 V RMS

Maximum DCR Unbalanced:

DCR Unbalance @ 20°C (%)
3

Electrical Characteristics-Premise (Overall)

Premise Cable Electrical Table 1:

Freq. (MHz)	Max. Attenuation (dB/100 m)	Min. NEXT (dB)	Min. PSNEXT (dB)	Min. ACR (dB)	Min. PSACR (dB)	Min RL (dB)	Min. SRL (dB)
1	2.0	65.3	62.3	63.0	60.3	20.0	23.0
4	4.1	56.3	53.3	51.0	49.2	23.0	23.0
8	5.8	51.8	48.8	46.0	43.0	24.5	24.5
10	6.5	50.3	47.3	43.0	40.8	25.0	25.0

METRIC MEASUREMENT VERSION

1585LC Multi-Conductor - Category 5e Nonbonded-Pair Cable

16	8.2	47.3	44.3	39.0	36.0	25.0	25.0
20	9.3	45.8	42.8	36.5	33.5	25.0	25.0
25	10.4	44.3	41.3	33.9	30.9	24.3	24.3
31.25	11.7	42.9	39.9	31.0	28.2	23.6	23.6
62.5	17.0	38.4	35.4	22.0	19.0	21.5	21.5
100	22.0	35.3	32.3	14.0	10.3	20.1	20.1
155	28.1	32.5	29.5	4.4	1.4	15.8	
200	32.0	30.8	27.8	4.0	1.0	15.0	

Premise Cable Electrical Table 2:

Freq. (MHz)	Input (Unfitted) Imp. (Ohms)	Fitted Impedance	Min. ELFEXT (dB)	Min. PSELFEXT (dB)
1	100 ± 15	100 ± 15	63.8	60.8
4	100 ± 15	100 ± 15	51.7	48.7
8	100 ± 15	100 ± 15	45.7	42.7
10	100 ± 15	100 ± 15	43.8	40.8
16	100 ± 15	100 ± 15	39.7	36.7
20	100 ± 15	100 ± 15	37.7	34.7
25	100 ± 15	100 ± 15	35.8	32.8
31.25	100 ± 15	100 ± 15	33.9	30.9
62.5	100 ± 15	100 ± 15	27.8	24.9
100	100 ± 15	100 ± 15	23.8	20.8
155	100 ± 25	100 ± 15	19.9	16.9
200	100 ± 25	100 ± 15	17.7	14.7

Notes (Overall)

Notes: Jacket sequentially marked at 2 ft. intervals. Thrid party verified to ANSI/TIA-568-C.2, Category 5e.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1585LC 006U1000	1,000 FT	23.000 LB	BLUE, LIGHT		CAT5E 4PR U/UTP LC BOX
1585LC 006I1000	1,000 FT	24.000 LB	BLUE, LIGHT	C	CAT5E 4PR U/UTP LC REEL
1585LC 009U1000	1,000 FT	23.000 LB	WHITE		CAT5E 4PR U/UTP LC BOX
1585LC 009I1000	1,000 FT	24.000 LB	WHITE	C	CAT5E 4PR U/UTP LC REEL

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 3 Revision Date: 08-14-2013

© 2015 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.