

Fuseholder Open Design, Holder for MSF 125, vertical, THT



125 V · 5 A (UL/CSA)



### Description

- Through hole mounting

### Standards

- UL 4248-1  
- CSA 22.2 no. 4248-1

### Approvals

- UL File Number: E39328

### References

Fuseholder to MSF 125; MSU 125

### Weblinks

[pdf-datasheet](#), [html-datasheet](#), [General Product Information](#), [Approvals](#), [CE declaration of conformity](#), [RoHS](#), [CHINA-RoHS](#), [REACH](#), [e-Shop](#), [SCHURTER-Stock-Check](#), [Distributor-Stock-Check](#), [Detailed request for product](#)

### Technical Data

|                              |                                |
|------------------------------|--------------------------------|
| Fuse-Link                    | Microfuse 125 V                |
| Mounting                     | PCB                            |
| Terminal                     | Solder THT                     |
| Rated Voltage                | 125V (UL/CSA)                  |
| Rated current                | 5A (UL/CSA)                    |
| Degree of Protection         | IP 40                          |
| Admissible Ambient Air Temp. | -40 °C to 85 °C                |
| Climatic Category            | 40/085/21 acc. to IEC 60068-1  |
| Material: Socket             | Thermoplastic, black, UL 94V-0 |
| Material: Terminals          | Silver-Plated Brass            |
| Unit Weight                  | 0.37 g                         |
| Storage Conditions           | 0 °C to 60 °C, max. 70% r.h.   |
| Product Marking              |                                |

|                              |  |
|------------------------------|--|
| Soldering Methods            | Wave   |
| Solderability                | 245 °C / 3 sec acc. to IEC 60068-2-20, Test Ta, method 1   |
| Resistance to Soldering Heat | 260 °C / 10 sec acc. to IEC 60068-2-20, Test Tb, method 1A |
| Contact Resistance           | < 5 mΩ at 20 mV  |
| Insulation Resistance        | > 10 MΩ between Life parts (500 VDC; 1 min)                |

### Dimension

8.3 mm



Variant 0031.7501

Drilling diagram

### All Variants

| Holder | Order Number |
|--------|--------------|
| ●      | 0031.7501    |

Most Popular.

Availability for all products can be searched real-time: <http://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER>

**Packaging Unit**    Plastic Bag (100 pcs.)

---