Frontpanel Switch, Momentary Action, Medium Stroke, 10 mm











Weblinks

html-datasheet, General Product Information, CE declaration of conformity, RoHS, CHINA-RoHS, e-Shop, CAD-Drawings, Product News, Detailed request for product

All Variants

Order Number Description

LDT 0041.9141

Availability for all products can be searched real-time:http://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER



5.SCHURTER

DATA LDT, LDS SWITCHES-MOMENTARY (LDT) AND LATCHING (LDS) ACTION

BENEFITS

- Absolute reliability and simple assembly
- Compact design with very small mounting depth
- Excellent price/performance ratio
- Suitable for front and print-mounting
- Good illumination
- Many different application fields


		LDT	LDS
Electrical data			
Switching voltage	[mV]	min. 100 AC / DC	min. 100 AC / DC
	[v]	max. 60 AC / 50 DC	max. 60 AC / 50 DC
Switching current max.	[mA]	200	200
Lifetime (at rated breaking capaci	ity 1.2W)	>105	>105
Initial contact resistance, new	[mΩ]	<20	<20
Initial contact resistance, after life	etime [mΩ]	<25	<25
Insulation resistance	[Ω]	>1010	> 1010
Contact bounce time	[ms]	typ. 0.5	typ. 0.5
Mechanical data			
Actuating force	[N]	1.2 ± 0.6	
Contact travel	[mm]	1.3 ± 0.5	
End contact travel	[mm]	2.9 ± 0.5	
End stop strength	[N]	>50	>50
Lifetime	[operations]	>105	>105
Other data			
Soldering method Hand soldering	g(soldering terminal)	or soldering bath(print terminals)	
Soldering heat resistance	[°C/s]	*280/3(soldering)270/5(print terminals)	*280/3(soldering)270/5(print terminals)
Ambient temperature	illuminated [ºC/s]	-25 -+60	-25 – +60
	non-illuminated [ºC/s]	-25 -+85	-25 - +85
Storage temperature	illuminated [ºC/s]	-25 -+60	-25 - +60
	non-illuminated [ºC/s]	-25 -+85	-25 – +85
Degree of protection		IP 40	IP 40
Materials			
Socket		Thermoplast PES	Thermoplast PES
Button		Thermoplast PC	Thermoplast PC
Contacts	gold on request	CuZn 37, mit 5 μm Ag	CuZn 37, mit 5 μm Ag
Contact spring		CuBe 37, mit 5 µm Ag	CuBe 37, mit 5 μm Ag
a a			



LED see page 29
Data refers to hand soldering only, not to be used for wave soldering

DIMENSIONS LDT, LDS SWITCHES-MOMENTARY AND LATCHING ACTION


CONSTRUCTION




LDT / LDS, small button


LDT / LDS, small button with solder terminal


DIMENSIONS







OTHER DATA










Wiring diagram


Front panel drilling

Drilling diagram

Solder terminal version

CIRCUIT DIAGRAM





NO 2 pole

23



5.SCHURTER

OVERVIEW LDT, LDS SWITCHES-MOMENTARY (LDT) AND LATCHING (LDS) ACTION



X in the Part No. must be replaced by the desired version With the illuminated version, the small button is transparent ""Securing clip must be ordered separately

OVERVIEW LDT, LDS SWITCHES-MOMENTARY (LDT) AND LATCHING (LDS) ACTION





In addition to the versions with the small button, further versions with a large button and switching functions are available on request.

LDT/LDS

LDT/LDS

FEATURES				
Illumination	non-illuminated	illuminated		
Models	small button with solder terminal	small button with solder terminal		
PART NUMBER *				
LDT NO 1 pole	0041.8841. x x 0 x	0041.8846. x x x x		
LDT NO 2 pole	0041.8842. x x 0 x	0041.8847. x x x x		
LDS NO 1 pole	0041.8851. x x 0 x	0041.8856. x x x x		
LDS NO 2 pole	0041.8852. x x 0 x	0041.8857. x x x x		
Colour of small button **				
red	3	3		
green	5	5		
black	7			
Shape of bezel/button				
round	1	1		
square	3	3		
Colour of LED				
red		1		
green		2		
Colour of bezel				
black	7	7		
Mounting accessories				
Securing clip***	0850	1.9242		
	Securing clip: Round bezel/ button:	square bezel/button:		

^{*} X in the Part No. must be replaced by the desired version
** With the illuminated version, the small button is transparent
***Securing clip is included





LETTERING

Depending on the application and font, there are various lettering possibilities. The following standards can be used for key letterings:

A =	001	P =	016	4 =	031	1 =	046	EIN = 06
B=	002	Q =	017	5 =	032	- → =	047	AUS = 06
C =	003	R=	018	6 =	033	←=	048	AUF = 06
D =	004	S =	019	7 =	034	↓ =	049	AB = 06
E=	005	T =	020	8 =	035		050	ON = 06
F=	006	U =	021	9 =	036	% =	051	OFF = 06
G =	007	V =	022	+=	037	√ =	052	UP = 06
H=	800	W =	023	-=	038	CTRL =	053	DOWN = 06
1 =	009	X =	024	•=	039	RETURN =	054	HIGH = 06
J=	010	Y =	025	x =	040	SHIFT =	055	LOW = 07
K =	011	Z =	026		041	LOCK =	056	ON/OFF = 07
L=	012	0 =	027	*=	042	STOP =	057	START = 07
M =	013	1 =	028		043	ENTER =	058	
N =	014	2 =	029	# =	044	BACK =	059	
0 =	015	3 =	030	e> =	045	LINE =	060	



MCS 18, LETTER HEIGHTS AND FONTS

- Single characters, Univers 65
- Legends max. 6 characters in line, Univers 65
- Insert label and front foil anthracite, RAL 7016
- Characters and symbols light grey, RAL 7035



SSM 27, LETTER HEIGHTS AND FONTS

- Single characters, Univers 65
- Legends max. 6 characters in line, Akzident-Grotesk condensed bold type
- Front foil anthracite, RAL 7016
- Characters and symbols light grey, RAL 7035



LIGHTING TECHNOLOGY

1. Maximum Ratings		LED old	LED new*	LED old	LED new*	LED old	LED new*
Internal part number		0925.9730		0925.9731		0925.9732	
Light colour		red	red	green	green	yellow	yellow
Forward current DC	l, max. [mA]	40	30	40	30	40	30
Power dissipation	P _{so} max. [mW]	130	100	130	100	130	100
2. Characteristics (ty	rp. At T _u =25°C)			1	(
Forward Voltage	at I, =10mA, U, typ. [V]	2.0 (<2.6)	2 at 20mA	2.0 (<2.6)	2.4 at 20mA	2.0 (<2.6)	2.4 at 20mA
Luminous intensity	at I _p =10mA, I _c typ. [mcd]	11.2 - 28	6.3 to	18 - 45	6.3 to	11.2 - 28	6.3 to
Viewing angle	typ. [degree]	50	60	50	60	50	60
Peak wave lenght	typ. [nm]	635	635	565	565	586	585
Reverse voltage	U, typ. [V]	5	6	5	6	5	6

29

