


230V Power Strip with 5-C13 Outlets, C14 Inlet, Switchless Design

MODEL NUMBER: **PS-5-INT**



Highlights

- 5 IEC-320-C13 outlets
- IEC-320 C14 inlet
- 10A resettable circuit breaker
- All-metal housing
- No power cord included. See [available cord sets](#)

Description

Tripp Lite's PS-5-INT Power Strip offers 10A capacity AC power distribution in a rugged all-metal outlet strip for 230V applications. Features 5 IEC-320-C13 outlets, 1 IEC-320-C14 inlet and built-in resettable circuit breaker. Switchless design prevents accidental shutoff.

Features

- 10A capacity AC power distribution in a rugged all-metal outlet strip for 230V applications
- 5 IEC-320-C13 outlets, 1 IEC-320-C14 inlet and built-in resettable circuit breaker
- Switchless design prevents accidental shutoff.

Specifications

General Info	
RoHS	Y
OVERVIEW	
Style	Strip
OUTPUT	
Output Receptacles	(5) C13
USB Charging	No
INPUT	
Nominal Input Voltage(s) Supported	230V AC



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Input Cord Length (ft.)	0
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	0
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	Yes
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Unit Dimensions (hwd / in.)	1.46 x 13.668 x 2.5
Unit Dimensions (hwd / cm)	3.708 x 6.350 x 34.717
Unit Weight (lbs.)	2.4
Unit Weight (kg)	1.09
Receptacle Color	Black
Outlets Measurement (Center to Center)	35.7mm
Keyhole Slot Mounting Measurement (Center to Center)	Distance between keyhole tabs = 203.20mm; Distance between end tabs = 330.17mm
SPECIAL FEATURES	
Right-Angle Plug	No
CERTIFICATIONS	
Certifications	Tested to IEC 60950
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.