

---

Item no.: 2002-1681  
Product description: WITH TESTING FACILITY

---



Produkt kann von Bild abweichen / product may differ

Packing unit 1 piece

RoHS compliant

Cross section to [AWG]	12 AWG
Cross section to [AWG]	12 AWG
Cross section [AWG]	22 - 22 AWG
Width	0.205 in
Cross section [mm <sup>2</sup> ]	0.25 - 0.25 mm <sup>2</sup>
Strip length	0.43 in
Height	1.299 in
Cross section to [mm <sup>2</sup> ]	2.5 mm <sup>2</sup>
Depth	2.618 in
Cross section to [mm <sup>2</sup> ]	4 mm <sup>2</sup>
Width	5.2 mm
Measured shock voltage	6 kV
Weight	7.698 g
Current intensity EN	10 A
Strip length from	10 mm
Strip length to	12 mm
Height	33 mm
Depth	66.5 mm
Measured voltage EN	400 V

No. of connection Points	2
No. of potentials	2
Connection method	CAGE CLAMP®S Connection



Wiring method	e+f
Pollution degree	3
Color	gray
Wiring type	Front-entry
Country of Origin	Deutschland
Safety information 1	The nominal voltage and nominal current are defined by the indicator lamp or the fuse.
Safety information 2	Blade-type fuses, please note touchproof protection from 42 V

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected