

Technical Data Sheet

Aquaseal® Fire-Alarm Cables

WEST PENN WIRE



2833 West Chestnut Street
 Washington, PA 15301
 Toll Free: (800) 245-4964
 Fax: (724) 222-6420
 www.westpenn-wpw.com



PART NUMBER:	AQ294
DESCRIPTION:	16/2 Stranded bare copper conductors, overall shield with Aquaseal tape and overall jacket.
NEC RATING:	FPL – PLTC, CL3 NEC Article 760 And 725
APPROVALS:	(UL) Listed – Direct Burial
APPLICATION:	Materials suitable for outdoor use, and indoor trays, allows a variety of uses for (Low voltage industrial process control circuits, Power-Limited circuits, Power-Limited fire alarm circuits, Power-Limited tray cable PLTC)

Construction Parameters:

Conductor	16 AWG Bare Copper
Stranding	7x24
Insulation Material	PVC with Nylon
Insulation Thickness	PVC 0.015" Nom. Nylon .005" Nom.
Number of Conductors	2 (1 Pair)
Shield	100% Aluminum Polyester Foil
Drain	Stranded Tinned Copper
Water-Blocking Tape	2 Ply water swellable tape
Jacket Material	Sunlight/ Moisture Resistant PVC
Jacket Thickness	0.040" Nom.
Overall Cable Diameter	0.328" Nom.
Approximate Cable Weight	58 Lbs/1M' Nom.
Flame Rating	UL 1685 Vertical Tray

Electrical & Environmental Properties:

Temperature Rating	-20deg C to 90deg C
Operating Voltage	300 V RMS
Max.Capacitance Between Conductors @ 1 KHz	37 pf/ft Nom.
Capacitance Between Conductors to Shield @ 1 KHz	67 pf/ft Nom.
DC Resistance per Conductor @ 20deg C	6.2 Ohms/1M' Nom.
Insulation Colors	Black, Red
Jacket Color	Black
RoHS Compliant	--
TIA455-82B Water Infiltration Test Compliant	Yes
UL 444 & 13 Compliant	Yes

Mechanical Properties:

Max. Recommended Pull Tension	69 lbs.
Min. Bend Radius (Install)	3.2"

Specification Issue Date: 7/06

This document is the property of West Penn Wire. The information contained herein is considered Proprietary and not to be reproduced by any means Without written consent of West Penn Wire

Standard Lengths are 1000ft.
 The Jacket is sequentially footmarked.
 The information presented here is, to the best of our knowledge, is true and accurate. However, since conditions of use are beyond our control, all recommendations or suggestions are presented without guarantee or responsibility on our part. We disclaim all liability in connection with the use of information contained herein or otherwise.