

## 15 x 32 Hour counters CHM15 Part number 99792810



- Capacity 100,000 hrs (99,999.99 hrs)
- Wide range of voltages : 4.5 →35 VDC
- Panel mounted
- IP65
- Highly resistant to shocks and impacts
- Compact size
- Excellent visibility thanks to the large digit size

### Part numbers

	Type	Operating frequency (Hz)	Voltages
99792810	CHM15	DC	4,5 →35 VDC


### Specifications

#### General characteristics

Counting capacity	99,999.99
Reset to zero	Not included
Read accuracy	1/100 h
Height digits (mm)	4
Colour of hour numbers	White on a black background
Colour of decimal digits	Red on a black background
Accuracy	VDC : < 0.003 % (24 hrs, 25 °C)
Counting input mode	Addition
Degree of protection front face	IP65
Mounting position	Horizontal readout of digits
Temperature limits use (°C)	-10 →+60
Temperature limits stored (°C)	-40 →+80
Certifications	CE - UL (pending)
Connections (panel mounted version)	Flying leads : 150 mm
Consumption	5 VDC approx. 82 mW/12 VDC approx. 135 mW/24 VDC approx. 135 mW/max 170 mW
Vibration resistance	50 m/s <sup>2</sup> (10-500 Hz) IEC 68-2-6
Test voltage for AC models	2 000 VAC 50 Hz
Weight (g)	20

### Dimensions (mm)

#### CHM15



### Dimensions (mm)

#### Panel cut-out

