

**HG 2310 LCD**

**Powerful, electronically controlled professional hot air gun with continuously adjustable air flow and temperature control.**

The tremendous power of the HG 2310 LCD makes it suitable for all hot-air jobs. The precision temperature display permits work on materials that respond critically to heat.



1. Visual display of temperature and speed on LCD
2. Selector button for 4 preset programmes
3. Memory button
4. Continuously adjustable temperature
5. Continuously adjustable air flow
6. Non-slip end cap

**Features**

- Sturdy casing for held-held and self-resting use
- Visual display of temperature and speed on LCD
- Four factory-set programmes:



- Double overheating protection: thermostat and thermal cut-out
- Air intake with lattice guard to keep out debris
- Soft grip handle and soft stand for stability

**Settings**

- Continuously adjustable airflow and temperature
- Capability of changing the four preset programmes as required

**HG 2310 LCD**

Prod. No.

**348311**

Dimensions (l x w x h)



260 x 90 x 205 mm

Voltage	230 V / 50 Hz
Output	2300 W
Temperature	stage 1: 50° C stage 2: 50 – 650° C
Display mode	LCD in 10° C steps
Blower	continuously adjustable
Airflow rate	stage 1: 150 – 250 l / min. stage 2: 150 – 500 l / min.
Programmes	factory set 1 = 250° C / approx. 350 l / min. 2 = 350° C / approx. 400 l / min. 3 = 450° C / approx. 500 l / min. 4 = 550° C / approx. 400 l / min.
Memory button	for changing preset programmes
Weight	940 g
	Also available in the sturdy plastic case!



Subject to technical modifications



print  close 

# Tool Set

## 129 Piece

**DURATOOL**



A 129 piece tool kit ideal for the household, supplied in a handy fold-up blow moulded carry case

### Contents:

- Wire Stripper
- Topedo level
- Knife
- 4 × Precision Screwdrivers
- 20mm × 25mm Bits
- Ratchet Handle
- 3.5m Tape measure
- 8oz Claw hammer
- 6" Adjustable wrench
- 6" Long nose pliers
- 6" Diagonal Pliers
- 16 × Hex keys

### Part Number Table

Description	Part Number
Set, Tool, 129 PC	D02154

**Important Notice** : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. DURATOOL is the registered trademark of the Group. © Premier Farnell plc 2012.

[www.element14.com](http://www.element14.com)  
[www.farnell.com](http://www.farnell.com)  
[www.newark.com](http://www.newark.com)  
[www.cpc.co.uk](http://www.cpc.co.uk)  
[www.mcmelectronics.com](http://www.mcmelectronics.com)

**DURATOOL**