



PL 123


Lithium/Manganese Dioxide



Nominal Voltage:	3.0 V
Typical Voltage:	3.2-3.3 V
Nominal Internal Impedance:	0.25 ohm @ 1kHz
Average Weight:	17.0 gm
Volume:	7.18 cm ³
Terminals:	Flat, Recessed Negative Terminal, Nickel Plated Steel
Operating Temperature Range:	-20°C to 75°C (-4°F to 167°F)
ANSI: IEC:	5018LC CR17345



Duracell Ultra 123 Typical Performance




* Delivered capacity is dependent on the applied load, operating temperature and cut-off voltage. Please refer to the charts and discharge data shown for examples of the energy / service life that the battery will provide for various load conditions.





PL 123

Lithium/Manganese Dioxide










Service (Hours)



DURACELL

Berkshire Corporate Park Bethel, CT 06801 U.S.A.

Telephone: Toll-free 1-800-544-5454 Internet: www.duracell.com

> * Delivered capacity is dependent on the applied load, operating temperature and cut-off voltage. Please refer to the charts and discharge data shown for examples of the energy / service life that the battery will provide for various load conditions.